

Earth leakage + Overcurrent + Short-circuit protection type

■ **SG series/3-pole JIS C8201-2-2**

Breaker ampere frame	Rated current (A)	Sensitive current 30mA	Sensitive current 100/200/500mA selectable	□ : Available mounting and connection
		Type	Type	
400	250	SG403RC/250-30MA□	SG403RC/250-CO□	Blank, X, E, P
	300	SG403RC/300-30MA□	SG403RC/300-CO□	
	350	SG403RC/350-30MA□	SG403RC/350-CO□	
	400	SG403RC/400-30MA□	SG403RC/400-CO□	
600	500	—	SG603RC/500-CO□	Blank, X, E, P
	600		SG603RC/600-CO□	
800	700	—	SG803RC/700-CO□	Blank, X, E, P
	800		SG803RC/800-CO□	

■ **SG series/4-pole JIS C8371**

Breaker ampere frame	Rated current (A)	Sensitive current 30mA	Sensitive current 100/200/500mA selectable	□ : Available mounting and connection
		Type	Type	
100	40	SGa104A/40-30MA□	SGa104A/40-CO□	Blank, X, E
	50	SGa104A/50-30MA□	SGa104A/50-CO□	
	60	SGa104A/60-30MA□	SGa104A/60-CO□	
	75	SGa104A/75-30MA□	SGa104A/75-CO□	
	100	SGa104A/100-30MA□	SGa104A/100-CO□	
100	50	SG104H/50-30MA□	SG104H/50-CO□	Blank, X, E
	60	SG104H/60-30MA□	SG104H/60-CO□	
	75	SG104H/75-30MA□	SG104H/75-CO□	
	100	SG104H/100-30MA□	SG104H/100-CO□	
225	125	SGa204A/125-30MA□	SGa204A/125-CO□	Blank, X, E
	150	SGa204A/150-30MA□	SGa204A/150-CO□	
	175	SGa204A/175-30MA□	SGa204A/175-CO□	
	200	SGa204A/200-30MA□	SGa204A/200-CO□	
	225	SGa204A/225-30MA□	SGa204A/225-CO□	
225	125	SG204H/125-30MA□	SG204H/125-CO□	Blank, X, E
	150	SG204H/150-30MA□	SG204H/150-CO□	
	175	SG204H/175-30MA□	SG204H/175-CO□	
	200	SG204H/200-30MA□	SG204H/200-CO□	
	225	SG204H/225-30MA□	SG204H/225-CO□	
400	250	SGa404A/250-30MA□	SGa404A/250-CO□	Blank, X, E
	300	SGa404A/300-30MA□	SGa404A/300-CO□	
	350	SGa404A/350-30MA□	SGa404A/350-CO□	
	400	SGa404A/400-30MA□	SGa404A/400-CO□	

Mounting	Connection	□
Front	Front	Blank
Front	Rear	X
Flush	Rear	E
Plug-in		P

Earth Leakage Case Breakers

Type number

Line protection

Earth leakage + Overcurrent + Short-circuit protection type

■ EG series/3-pole JIS C8201-2-2

Breaker ampere frame	Rated current (A)	Sensitive current 100/200/500mA selectable	☐ : Available mounting and connection
		Type	
600	500 600	EG603C/500-CO ☐ EG603C/600-CO ☐	Blank, X, E, P
800	700 800	EG803C/700-CO ☐ EG803C/800-CO ☐	Blank, X, E, P

Mounting	Connection	☐
Front	Front	Blank
Front	Rear	X
Flush	Rear	E
Flush	Top and bottom	Y
Plug-in		P

■ EG series/4-pole (3P+1N) JIS C8201-2-2

Front mounting, front connection

Breaker ampere frame	Rated current (A)	Sensitive current 30mA	Sensitive current 100mA	Sensitive current 300mA	Sensitive current 500mA
		Type	Type	Type	Type
100	30 40 50 60 75 100	EG104A/30-30MA EG104A/40-30MA EG104A/50-30MA EG104A/60-30MA EG104A/75-30MA EG104A/100-30MA	EG104A/30-100MA EG104A/40-100MA EG104A/50-100MA EG104A/60-100MA EG104A/75-100MA EG104A/100-100MA	EG104A/30-300MA EG104A/40-300MA EG104A/50-300MA EG104A/60-300MA EG104A/75-300MA EG104A/100-300MA	EG104A/30-500MA EG104A/40-500MA EG104A/50-500MA EG104A/60-500MA EG104A/75-500MA EG104A/100-500MA