



Fluke 62/322/1AC IR Thermometer, Clamp Meter and Voltage Detector Kit

- Available inventory
- Fluke store
- Register products
- Download manuals



Contact me about this product
Request a product demonstration

Search Fluke

Resources Products

Find Resources

Model name	Description	Buy it **
Fluke 62	Infrared Thermometer <ul style="list-style-type: none"> Best accuracy in its class: $\pm 1.5\%$ of reading Wide temperature range from -30°C to 500°C (-20°F to 932°F) Single point offset laser sighting Backlit display for poorly lit areas 	
Fluke 322	Clamp Meter <ul style="list-style-type: none"> Resolution up to 0.01 A and 0.1 V Measures ac current to 400 A Measures ac volts to 600 V, dc volts to 600 V Resistance measurement to 400 Ω, continuity checking 	
Fluke 1AC II	VoltAlert Voltage Detector <ul style="list-style-type: none"> Voltbeat™ technology and continuous self-test so you always know it's working Upon detection of voltage, tip glows and beeper sounds CAT IV 1000 V for added protection Expanded range: 90 V to 1000 V ac 	

© 1995 – 2009 Fluke Corporation

*