



*Quality Products. Service Excellence.*

## Type 4X Stainless Steel Junction Box 1414 N4 PH SS Series

Continuous Hinge Door with Clamps



### Application

- Designed for use as instrument enclosures, electric, hydraulic or pneumatic control housings, electrical junction boxes or terminal wiring enclosures.
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion may be a problem.

### Standards

- UL 508A Type 3R, 4, 4X, 12 and 13
- CSA Type 3R, 4, 4X, 12 and 13
- Complies with
  - NEMA Type 3R, 4, 4X, 12 and 13
  - IEC 60529, IP66

### Construction

- Formed from 14 gauge 304 or 316 stainless steel.
- Smooth, continuously welded seams.
- Welded brackets provide for enclosure mounting.
- Continuous stainless steel hinged cover is secured with stainless steel clamps and screws.
- Seamless poured-in place gasket.
- All models include a removable 14 gauge inner panel.
- Tapped studs are provided for mounting inner panels.
- A bonding stud is provided on the door and a grounding stud is provided in the enclosure

### Finish

- Cover and enclosure are natural stainless steel with a smooth brushed finish.
- Removable inner panel is finished in white powder coating.

### Accessories

- Additional Inner Panels
- Terminal Kit Assemblies
- Junction Box Quick Release Clamp
- Climate Control
- Swing Panel Kit
- Door Clamping Hardware
- Junction Box Padlock Kit
- General Accessories

**New and improved PDF part drawing files with more detail now available.**

Click part number in table below to access PDF, DXF, and STEP files.

304 S.S. Part No:	316 S.S. Part No:	Enclosure			Panel	
		H	W	D	H	W
1414N4PHSSC4	1414N4PHS16C4	6.00	4.00	4.00	4.88	2.88
1414N4PHSSE	1414N4PHS16E	6.00	6.00	4.00	4.88	4.88
1414N4PHSSG	1414N4PHS16G	8.00	6.00	3.50	6.75	4.88
1414N4PHSSG4	1414N4PHS16G4	8.00	6.00	4.00	6.75	4.88
1414N4PHSSI	1414N4PHS16I	10.00	8.00	4.00	8.75	6.88
1414N4PHSSK	1414N4PHS16K	12.00	10.00	5.00	10.75	8.88
1414N4PHSSK6	1414N4PHS16K6	12.00	10.00	6.00	10.75	8.88
1414N4PHSSL6	1414N4PHS16L6	12.00	12.00	6.00	10.75	10.88
1414N4PHSSM6	1414N4PHS16M6	14.00	12.00	6.00	12.75	10.88
1414N4PHSSO6	1414N4PHS16O6	16.00	14.00	6.00	14.75	12.88
1414N4PHSSM8	1414N4PHS16M8	14.00	12.00	8.00	12.75	10.88
1414N4PHSSO10	1414N4PHS16O10	16.00	14.00	10.00	14.75	12.88

*Data subject to change without notice*

© 2019. Hammond Manufacturing Ltd. All rights reserved.