



Quality Products. Service Excellence.

Water-Tight Hand-Held Enclosures 1553W Series

IP 65 Protection, Soft Sides



Key Features:

- Ergonomically designed for hand-held comfort.
- Designed to meet IP65.
- Uses a one piece silicone gasket (installed). Enclosure utilizes tongue & groove construction - molded into the top & bottom halves.
- Choice of three sizes - in two colors.
- Molded in flame retardant - ABS plastic (FRABS) - UV stabilized. With a grey overmold, soft plastic grip.
- Top cover is recessed for membrane display or keypad.
- P.C. board standoffs are molded into both the top & bottom of the enclosure (see drawings or photos for more details). Standoff screws (M2) not included.
- Front panel is an integral part of the top half of the enclosure.
- Choice of two enclosure colors, light grey or black - soft side "grip" plastic color is grey.
- Enclosure is secured with black Philips, stainless steel, machine screws, threaded into integral brass bushings. Perfect for applications when repetitive assembly and disassembly are required.
- Assembly hardware included - for replacement part numbers - see individual drawings.
- 100-pack of PC board screws, part number **1553WTS100**
- Replacement assembly screws for sizes "B" and "D", part number **SC1553WB100BK** (100-pack, black stainless steel)
- Replacement assembly screws for sizes "C", part number **SC1553WC100BK** (100-pack, black stainless steel)
- For similar enclosures designed for general purpose applications, including more size and colors options, try series **1553**

Photo Features



Recessed Top



Key Internal Features



Three sizes



Light Grey or Black Enclosure Color

Part Numbers

| Part Number | Color | Battery Door & Compartment | Length | Width | Depth (assembled) | Replacement Gasket (2-pack) |
|-------------|-------|----------------------------|--------|-------|-------------------|-----------------------------|
| 1553WBBK | Black | No | 4.62 | 3.11 | 0.98 | 1553WBGASKET |
| 1553WBGY | Grey | No | 4.62 | 3.11 | 0.98 | 1553WBGASKET |
| 1553WCBK | Black | No | 4.62 | 3.11 | 1.26 | 1553WCGASKET |
| 1553WCGY | Grey | No | 4.62 | 3.11 | 1.26 | 1553WCGASKET |
| 1553WDBK | Black | No | 5.80 | 3.54 | 0.98 | 1553WDGASKET |
| 1553WDGY | Grey | No | 5.80 | 3.54 | 0.98 | 1553WDGASKET |

Data subject to change without notice

© 2019. Hammond Manufacturing Ltd. All rights reserved.