

Pre-Assembled C4 Cabinet *C4RR Series*



When you need cabinets quickly, our pre-assembled C4RR are a great option. Based off of our most popular requested configurations, each cabinet is factory configured and is packaged ready-to-ship. [Click here to view our C4 Series' components.](#)

Specifications

- Constructed in:
 - 14-gauge steel (body).
 - 16-gauge steel (doors and side panels).
 - 10-gauge tapped rails, 12-gauge square hole punched rails.
- EIA-310-D compliant 10-32 tapped or square hole punched rails with rack unit labels.
- Infinite-depth setting using C-channel struts.
- Zinc-plated mounting rails provide superior surface areas for equipment grounding.
- The 30" wide C4 rails have cable-tie support and pass-through holes.
- Four (4) leveling feet are included with support for optional casters.
- Grounding studs provided on frame as well as side panels and doors.

Specifications

- Complies with Seismic IBC 2012 Zone-4 standards when used with **C4K-Z4** Seismic Bolt Down Kit.
- Finished in textured black powder paint. Also available in textured white upon request.
- Tested to nearly double the suggested load rating of 2,000 lbs.
- Structurally adequate to safely resist 1,000 lbs of equipment and self-weight in seismic zone.
- RoHS Compliant.
- Manufactured in North America.

Included Components

- All configurations include:
 - One (1) Welded C4 Cabinet Frame with Top Cable Entry Holes
 - Two (2) Removable Side Panels (with 1/4 turn latches)
 - Four (4) Leveling Feet
 - Eight (8) Keys
 - Starter pack of 10-32 Screws (and cage nuts when applicable).
- **C4RR Data Cabinet Specific Components include:**
 - Two (2) Pairs infinitely adjustable square hole rails
 - One (1) Plexi Front Door
 - One (1) Perforated Rear Door
 - One (4) Fan cutout Top Panel
 - One (1) Vertical Cable Tray with Toolless PDU Mounting

- **C4RR Server Cabinet Specific Components include:**
 - Two (2) Pairs infinitely adjustable square hole rails
 - One (1) Perforated Front Door
 - One (1) Split Perforated Rear Door
 - One (4) Fan cutout Top Panel
 - Two (2) Vertical Cable Trays with Toolless PDU Mounting

Updates

- **24-Mar-2014:** The mounting rails for this product are getting a new and improved Silver Zinc Steel Plate treatment. This is a rolling change and the traditional yellow Zinc plating is available while supplies.

Accessories

Cabinet Fan Tops	Side Panel Locking Kit
Vertical Cabinet Cable Manager with Door	Universal Rack Shelf
Four Post Fixed Depth Shelf	Four Post Mounting Zero Space Fixed Shelf
Adjustable Depth 4-Post Rack Mount Shelf	Four Post Mounting Sliding Shelf
Rack Mount Locking Storage Drawer	Rack Unit Label
Sliding Keyboard Shelf	Adjustable Depth Cable Manager
Horizontal Lacing Strip	Horizontal Ring Cable Manager
Horizontal Hinged Cable Manager	Horizontal Steel Finger Cable Manager
Horizontal Hinged Cable Guide	Vertical Cable Tray
Mounting Hardware	Rack Panels
Outlet Strips	Grounding
Caster Set	

C4RR Data Cabinet

Part No.	Overall Dimensions			Rack Units	Usable Mounting Dimensions		
	Height	Width	Depth		Height	Width	Depth
C4RR247331DBK1	78.00	24.00	31.50	42U	73.50	19.00	29.50
C4RR247336DBK1	78.00	24.00	36.00	42U	73.50	19.00	34.00
C4RR247342DBK1	78.00	24.00	42.00	42U	73.50	19.00	40.00
C4RR247731DBK1	83.75	24.00	31.50	44U	77.00	19.00	29.50
C4RR247736DBK1	83.75	24.00	36.00	44U	77.00	19.00	34.00
C4RR247742DBK1	83.75	24.00	42.00	44U	77.00	19.00	40.00
C4RR307731DBK1	83.75	30.00	31.50	44U	77.00	19.00	29.50
C4RR307736DBK1	83.75	30.00	36.00	44U	77.00	19.00	34.00
C4RR307742DBK1	83.75	30.00	42.00	44U	77.00	19.00	40.00

C4RR Server Cabinet

Part No.	Overall Dimensions			Rack Units	Usable Mounting Dimensions		
	Height	Width	Depth		Height	Width	Depth
C4RR247331SBK1	78.00	24.00	31.50	42U	73.50	19.00	29.50
C4RR247336SBK1	78.00	24.00	36.00	42U	73.50	19.00	34.00
C4RR247342SBK1	78.00	24.00	42.00	42U	73.50	19.00	40.00

Part No.	Overall Dimensions			Rack Units	Usable Mounting Dimensions		
	Height	Width	Depth		Height	Width	Depth
C4RR247731SBK1	83.75	24.00	31.50	44U	77.00	19.00	29.50
C4RR247736SBK1	83.75	24.00	36.00	44U	77.00	19.00	34.00
C4RR247742SBK1	83.75	24.00	42.00	44U	77.00	19.00	40.00
C4RR307731SBK1	83.75	30.00	31.50	44U	77.00	19.00	29.50
C4RR307736SBK1	83.75	30.00	36.00	44U	77.00	19.00	34.00
C4RR307742SBK1	83.75	30.00	42.00	44U	77.00	19.00	40.00

Data subject to change without notice

© 2014. Hammond Manufacturing Ltd. All rights reserved.