

Path: [Home](#) > [Enclosure Index](#) > [ROLEC-HAMMOND Aluminum Product Index](#) > Round R280 aluDISC Series



Key Features:

- Round - modern, high quality instrument enclosure
- Material - Aluminum die-cast: GD SI 12 / DIN 1725
- Shallow lid, deep body
- Captive stainless steel lid screws
- Enclosure can be mounted to wall or shelf after closing the lid
- Integrated 1.7 mm recess in lid for membrane keypads and front panels
- Silicone gasket standard. (-50°C up to +140°C)
- Dark grey plastic clip-on design covers - to hide mounting & lid screws (plastic - polyoxymethylene) - RAL 7016
- Complete with lid captivation devices
- Degree of protection: NEMA 4X, IP 66 & IP67
- Textured polyester powder coat, light grey RAL 7035. (can be supplied unpainted on special order)

Part Number	 Reader File	AutoCAD .dxf File	3D Solid Model .igs & .stp files (zipped)	Units	Length	Width	Depth (Including Lid)
R280-080-000	<i>NEW</i>	<i>NEW</i>	<i>NEW</i>	mm	110	97	55
				inches	4.3	3.8	2.1
R280-100-000	<i>NEW</i>	<i>NEW</i>	<i>NEW</i>	mm	130	119	65
				inches	5.1	4.7	2.5
R280-120-000	<i>NEW</i>	<i>NEW</i>	<i>NEW</i>	mm	150	139	80
				inches	5.9	5.5	3.1
R280-160-000	<i>NEW</i>	<i>NEW</i>	<i>NEW</i>	mm	190	179	90
				inches	7.5	7.0	3.5

Features (by photos):



click to enlarge
 Snap in design covers hide both lid screws and installation holes



click to enlarge
 Integrated recesses for membrane keypads.



click to enlarge
 Enclosure can be installed after closing lid



click to enlarge
 Standoffs in the enclosure and lid for panels, P.C. boards & components.

Exactly what you are looking for???
 Link to our stocking distributors – most have "on-line" pricing, stock check and ordering!!!

Our Distributors

[Order from your favorite distributor](#)