



Quality Products. Service Excellence.

Eclipse Rack Panel *ERP Series*

For use with Eclipse Enclosure Series

Features



- Provides 19" rack mounting with full EIA spacing (punched holes).
- Rack mounting units available in 4U, 6U and 8U (mounting rails not included).
 - Rails pivot 180 degrees for easy equipment mounting.
- Includes starter pack of mounting hardware and panel installation hardware.
- Maintains UL, CSA and NEMA ratings when field installed.
- Smooth black powder paint finish.
- RoHS Compliant.
- Manufactured in North America.

Ordering Notes

- **The ERP was designed for use with the HLP*UR swivel rail system.**
- **Be sure to order the ERP that fits your enclosure and the desired HLP*UR.**



Mild Steel Enclosure Comparability

Compatible ERP Part No.	Optional Mounting Rail Compatibility			ANSI 61 Gray Mild Steel Solid Door	RAL7035 Light Gray Mild Steel Solid Door	ANSI 61 Gray Mild Steel Window Door	RAL7035 Light Gray Mild Steel Window Door	Overall Enclosure Dimensions		
	4U Rail Part No.	6U Rail Part No.	8U Rail Part No.	Part No.	Part No.	Part No.	Part No.	A	B	C
ERP2424	HLP4UR	n/c	n/c	-	-	EN4SD242412WGY	EN4SD242412WLG	24.00	24.00	12.00
ERP2424	HLP4UR	HLP6UR	n/c	EN4SD242416GY	EN4SD242416LG	EN4SD242416WGY	EN4SD242416WLG	24.00	24.00	16.00
ERP2424	HLP4UR	HLP6UR	HLP8UR	EN4SD242420GY	EN4SD242420LG	EN4SD242420WGY	EN4SD242420WLG	24.00	24.00	20.00
ERP3024	HLP4UR	n/c	n/c	EN4SD302412GY	EN4SD302412LG	EN4SD302412WGY	EN4SD302412WLG	30.00	24.00	12.00
ERP3024	HLP4UR	HLP6UR	n/c	EN4SD302416GY	EN4SD302416LG	-	-	30.00	24.00	16.00
ERP3024	HLP4UR	HLP6UR	HLP8UR	EN4SD302420GY	EN4SD302420LG	EN4SD302420WGY	EN4SD302420WLG	30.00	24.00	20.00
ERP3024	HLP4UR	HLP6UR	HLP8UR	EN4SD302424GY	EN4SD302424LG	-	-	30.00	24.00	24.00
ERP3624	HLP4UR	n/c	n/c	EN4SD362412GY	EN4SD362412LG	-	-	36.00	24.00	12.00

n/c = Not Compatible

Stainless Steel Enclosure Comparability

Compatible ERP Part No.	Optional Mounting Rail Compatibility			White Stainless Steel Solid Door	304 Gauge Stainless Steel Solid Door	316 Gauge Stainless Steel Solid Door	304 Gauge Stainless Steel Window Door	Overall Enclosure Dimensions		
	4U Rail Part No.	6U Rail Part No.	8U Rail Part No.	Part No.	Part No.	Part No.	Part No.	A	B	C
ERP2424	HLP4UR	n/c	n/c	EN4SD242412SSWH	EN4SD242412SS	EN4SD242412S16	-	24.00	24.00	12.00
ERP3024	HLP4UR	n/c	n/c	-	EN4SD302412SS	EN4SD302412S16	EN4SD302412WSS	30.00	24.00	12.00
ERP3024	HLP4UR	HLP6UR	n/c	-	EN4SD302416SS	-	-	30.00	24.00	16.00
ERP3624	HLP4UR	n/c	n/c	-	EN4SD362412SS	EN4SD362412S16	-	36.00	24.00	12.00

n/c = Not Compatible

Sloped Stainless Steel Enclosure Comparability

Compatible ERP Part No.	Optional Mounting Rail Compatibility			304 Gauge Stainless Steel Solid Door	Overall Enclosure Dimensions			
	4U Rail Part No.	6U Rail Part No.	8U Rail Part No.	Part No.	A1	A2	B	C
ERP2424	HLP4UR	n/c	n/c	ST242412SS	24.00	28.30	24.00	12.00
ERP3024	HLP4UR	n/c	n/c	ST302412SS	30.00	34.30	24.00	12.00

n/c = Not Compatible

Data subject to change without notice

© 2019. Hammond Manufacturing Ltd. All rights reserved.