





(4X) SNAP-IN  
POLYCARBONATE  
HINGE KNUCKLE

FIP  
POLYURETHANE  
GASKET


SECTION C-C

MATERIAL:  
BOX: INJECTION POLYCARBONATE  
STANDARD COVER: INJECTION POLYCARBONATE  
CLEAR COVER: INJECTION POLYCARBONATE




SECTION D-D

OPTIONAL BACK PANEL  
0.100[2.54] TH'K - ALUMINUM  
0.075[1.91] TH'K - PAINTED STEEL  
0.188 [4.78] TH'K-PVC



(2X) POLYCARBONATE  
FLANGES (GLUED)

(6X) #10-32 BRASS INSERTS,  
316 STAINLESS STEEL FLANGE  
AND FEET SCREWS




FRONT VIEW WITH  
COVER REMOVED

(2X) 316 STAINLESS  
STEEL LOCKABLE  
SNAP LATCHES

.19 [4.8]  
WALL THICKNESS

(4X) #10-32 BRASS  
INSERTS AND PLATED  
CARBON STEEL TRUSS SCREWS

NOTE:  
1. DATA SUBJECT TO CHANGE



PART No. PCJ181610CCLF

for more information visit  
[www.hammfg.com](http://www.hammfg.com)  
Data subject to change without notice  
Drawing Not to Scale