

Path: [Home](#) > [Enclosure Index](#) > Tablet Enclosures - Flame Retardant ABS

Non-Battery Door Version
(black model shown)

Battery Door Version
(gray model shown)



click to enlarge



click to enlarge



click to enlarge

For video information link to: 

Key Features:

- Low profile - ergonomically designed for a comfortable fit into the user's hands.
- Perfect for instrument or mobile data enclosures requiring a touch screen.
- Choice of two sizes - both available with or without battery compartment.
- Molded from **flame retardant ABS plastic**, choice of black (RAL 9011) or grey (RAL 7035) - material carries a UL flammability rating of 94V-0.
- Enclosure is assembled with six (6) - M3-0.5 x 18 mm Philips machine screws, threaded into integral brass bushings. Perfect for applications when repetitive assembly and disassembly are required.
- Integral brass bushings are factory inserted into the top half of the enclosure (see photos).
- Lap joint construction provides protection against access of dust and splashing water. Designed to meet IP54.
- P.C. board standoffs are molded into case top & bottom halves (see drawings or photos for more details).
- Battery door & compartment version (part numbers ending in "BAT") includes 8 battery clips (for 4 - AA batteries) and two 9 volt (PP3) battery clips.
- Contains one end panel - removable for easy modification.
- Bottom half of enclosure includes a square - molded inlay for labels (see drawings for details).

Flame Retardant ABS Plastic


Part Number	Color	PDF Reader File	AutoCAD .dwg Files (zipped)	3D Solid Model .stp & .igs files (zipped)	Battery Door & Compartment	Removable End Panel	Overall Enclosure Dimensions			
							Units	Length	Width	Enclosure Depth
1599TABMBK 1599TABMGY	Black				No	Yes	Inches	6.67	5.31	1.06
	Grey	459K	275K	1,010K			mm	170	135	27
1599TABMBKBAT 1599TABMGYBAT	Black				Yes	Yes	Inches	6.67	5.31	1.06
	Grey	510K	311K	1,356K			mm	170	135	27
1599TABLBK 1599TABLGY	Black				No	Yes	Inches	9.45	7.48	1.18
	Grey	430K	350K	510K			mm	240	190	30
1599TABLBKBAT 1599TABLGYBAT	Black				Yes	Yes	Inches	9.45	7.48	1.18
	Grey	482K	254K	764K			mm	240	190	30

 Link here to [photo tables](#) of each part number



Features (by photo):

Battery Door & Compartment Versions
(Part numbers ending in "BAT")

Includes our long life 3 point battery door.
Compartment takes either four (4) AA batteries or two (2) 9V (PP3) batteries



click to enlarge

Battery compartment (includes 8 clips) for four AA batteries.	Battery compartment (includes 2 clips) for 9V (PP3) batteries.
 <p>click to enlarge</p>	 <p>click to enlarge</p>

Accessories

Part Number	Thumbnail Photo	Color	Package Quantity	Description
1594MS100		Silver	100	Replacement Cover Screws (M3-0.5 x 18mm Flat Head)
1594MS100BK		Black	100	Replacement Cover Screws (M3-0.5 x 18mm Flat Head)
1593ATS50		Silver	50	Optional P.C. Board Screws (#4 x 1/4" Self Tapping)
1593ATS100		Silver	100	Optional P.C. Board Screws (#4 x 1/4" Self Tapping)

Exactly what you are looking for???

Link to our stocking distributors – most have "on-line" pricing, stock check and ordering!!!

[Our Distributors](#)

[Order from your favorite distributor](#)