

[About Abbatron](#)

[Locate Distributor or Representative](#)

[Contact / Sample Request](#)

Solder Lug
[1488-6]

Check Inventory for this item

This product is certified ROHS compliant

Product Specifications

Center:	23/64
Hole:	1/16
Length:	9/16
O.D.:	1/4
Stud Size:	6
Thickness:	.010
Width:	5/32

Catalog Search

Use keywords to find the product you are looking for

Inventory Search

Enter a product id to search current inventory.

This product was added to our catalog on Wednesday 16 January, 2009

Cross Reference Lookup

Enter a product id to search current inventory.

Monday 06 July, 2009

663962 requests since Sunday 04 November, 2008

Copyright © 2009 [Abbatron Online Catalog](#)
Powered by [psCommerce](#)

[Coaxial Antenna Connector:](#)

[Receptacles](#)

[RF Connectors](#)

[MMCX Board Connectors](#)

[MMCX Cable Connectors](#)

[SMA 50 Ohm Connectors](#)

[SMA Board Level Connectors](#)

[Bumpers and Chassis Feet](#)

[Cable Clamps and Strain Reliefs](#)

[Caterpillar Grommets](#)

[Grommets](#)

[High Voltage Insulators](#)

[Hole Plugs](#)

[Instrument Handles](#)

[Insulated Washers](#)

[Shaft Accessories](#)

[Solder Lugs and Terminals](#)

[Terminal Strips](#)

[Cable Clamps](#)

[Fahnestock Clips](#)

[Wire Strain Reliefs](#)

[Nylon Hole Plugs](#)

[Steel Hole Plugs](#)

[Bushing Extenders](#)

[Panel Bearings](#)

[Shaft Couplers](#)

[Shaft Locks](#)

[Binding Post Style](#)

[Miniature](#)

[Solder Lug With Base](#)

[Standard Size](#)

[Binding Posts](#)

[Jacks](#)

[Plugs](#)

[Dual Binding Posts](#)

[Insulated Binding Posts](#)

[Knob Type Binding Posts](#)

[Metal Binding Posts](#)

[Miniature Binding Posts](#)

[Spring Loaded Binding Post:](#)

[Insulated Banana Jacks](#)

[Insulated Tip Jacks](#)

[Printed Circuit Test Jacks](#)

[Uninsulated Banana Jack](#)

[Uninsulated Tip Jacks](#)

[Giant Banana Plugs](#)

[Insulated Banana Plugs](#)

[Phone Tip Plugs](#)

[Standard Insulated Banana Plug](#)

[Uninsulated Banana Plugs](#)

[Insulated Phone Tips Plugs](#)

[Uninsulated Phone Tip Plug](#)

[Aluminum Hex Standoffs](#)

[Aluminum Male/Female Hex Standoff](#)

[Aluminum Round Spacers](#)

[Aluminum Round Standoffs](#)

[Brass Hex Standoffs](#)

[Brass Male/Female Hex Standoffs](#)

[Brass Male/Male Adapters](#)

[Brass Round Spacers](#)

[Brass Round Standoffs](#)

[Brass Swivel Standoffs](#)

[Ceramic Standoffs](#)

[Nylon Hex Threaded Standoffs](#)

[Nylon M/F Hex Threaded Standoff](#)

[Nylon Round Spacers](#)

[Nylon Round Threaded Standoffs](#)

[Phenolic Spacers](#)

[Alligator Clips](#)

[Dual Instrument Test Adapter](#)

[Jumpers](#)

[Test Lead Kits](#)

[Test Leads](#)

[Test Prods](#)