



GFP20M -- Circuit Guard® Multiple Outlet Portable GFCI



4 Outlet, Yellow

GFP15M

Product Specifications	
GFCI Product Type	 Multi-Outlet GFCI
Amperage	20A
Color	 Yellow
Voltage	125V AC
Set Style	Automatic
Cord Length	6'
Device Style	Straight Blade
Trip Level	4-6 mA
Trip Time	0.025 seconds
Frequency	60Hz
Voltage Range	120V AC +10% -15%
Max Humidity	0.95
Operating Temp	Deg F -30 to 150 (Deg C -30 to 66)
UPC Number	78358552110
Weight in LBs	3.8
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

