

# GFP25C15A -- Circuit Guard® Automatic Set Portable GFCI Line Cord



25' GFCI automatic set line cord.

GFP4C15A

Product Specifications	
GFCI Product Type	<p>GFCI Line Cords</p>
Line Cord Type	Industrial
Amperage	15A
Color	<p>Yellow</p>
Voltage	125V AC
Set Style	Automatic
Cord Length	25'
Device Style	Straight Blade
Cord Ends	Male Plug/ Female Connector
Trip Level	4-6 mA
Trip Time	0.025 seconds
Frequency	60Hz
Voltage Range	120V AC +10% -15%
Max Humidity	0.95
Operating Temp	Deg F -30 to 150 (Deg C -30 to 66)
UPC Number	78358582955
Weight in LBs	3.45
Link to Drawing Library	<a href="#">Click here for Library</a>
Link to PDF Catalog	<a href="#">Click here for Catalog</a>

