



Communication Solutions for Harsh Environments

HI-IMPACT™

HI-Impact™ Connectors

Call for additional product information



Type	Cat. No.
Cat 6	HI6*
Cat 5e	HI5E
Cat 5e In-Line Coupler	HI5EC
Cat 5e Shielded	HI5ESC
M12 MicroQuick, 4-position, Male	MBMS14314HI*

* Available Q2-2004.

Communication Jacks



Description	Cat. No.
Category 6	HXJ6XX
Category 5e	HXJ5EXX

XX = Color

BK = Black
GY = Gray
OR = Orange
W = White

B = Blue
GN = Green
R = Red
Y = Yellow

EI = Electric Ivory
OW = Office White
TI = Telco Ivory

Multimedia Connector

Description	Cat. No.
F-type	HIF**

** Available Q3-2004.



Connector Cover

Description	Cat. No.
Protective Cover	HIC



HI-Impact™ Frames

Call for additional product information

StyleLine® Frames

Ports	Cat. No.
2	ISF2XX
3	ISF3XX
4	ISF4XX
6	ISF6XX



Duplex Frames

Ports	Cat. No.
2	BR106XX
4	Q106XX



xx = Color

BK = Black
GY = Gray
W = White

EI = Electric Ivory
OW = Office White

HI-Impact™ Plates

Call for additional product information

Stainless Steel

Ports	Gang	Cat. No.
1	1	HISF11
2	1	HISF12
2	2	HISF22
4	2	HISF24



Thermoplastic, 4-Point FS/FD, 1-Gang

Ports	Color	Cat. No.
1	Gray	HI14GY
2	Gray	HI24GY
1	Yellow	HI114PY
2	Yellow	HI124PY



Flip-Cover, Die-Cast Aluminum, Vertical, 1-Gang

Type	Cat. No.
Device	WP26HI
FS/FD	WPFS26HI



Flip-Cover, Thermoplastic, Vertical, 1-Gang

Type	Cat. No.
Device	HBL5222HI
FS/FD	HBL5221HI



Weatherproof, NEMA 3R



Horizontal	Gang	Cat. No.
Weatherproof	1	WP826MHPHI

Vertical	Gang	Cat. No.
Weatherproof	1	WP826MPHI
Weatherproof	2	WP8262MPHI



Vertical	Gang	Cat. No.
Secure-IT™	1	TWPF1GY

HI-Impact™ Boxes

Call for additional product information



Fiberglass Weatherproof Device Box with Lugs

Knockout	Color	Cat. No.
3/4"	Yellow	HBL60CM83HI

Cast Aluminum Device Box with Lugs

Knockout	Color	Cat. No.
1/2"	Gray	HIFD1L*
3/4"	Gray	HIFD2L*

* Available Q2-2004.

Cast Aluminum Weatherproof Device Box with Lugs

Knockout	Color	Cat. No.
1/2"	Gray	HIWP05GY*
3/4"	Gray	HIWP75GY*

* Available Q2-2004.

NEMA 4X Box

Thermoplastic, Gray

Ports	Cat. No.
1	HI14XGY*
2	HI24XGY*
4	HI44XGY*
6	HI64XGY*



Stainless Steel

Ports	Cat. No.
1	HI1CBSS*
2	HI2CBSS*

* Available Q2-2004.



NEMA 4/12 Box

Stainless Steel, Gray

Port	Cat. No.
1	HI1CBG*
2	HI2CBG*

* Available Q2-2004.



Portable Outlet with Strain Relief Kit

Port	Cat. No.
1	HI1POB*
Multiport	HIPOB*

* Available Q3-2004.

HI-Impact™ Cords

Call for additional product information



HI-Impact to HI-Impact Connector

Type	Cat. No.
Cat 6	HI6XXEE*
Cat 5e	HI5EXXEE
Cat 5e, Shielded	HI5ESXXEE**
F-type	HIFXXEE**
M12, 4-position female	HIM12XXEE**



HI-Impact Connector to RJ-45

Type	Cat. No.
Cat 6	HI6XXAE*
Cat 5e	HI5EXXAE
Cat 5e, Shielded	HI5ESXXAE**
F-type	HIFXXAE**
M12, 4-position female	HIM12XXAE**



HI-Impact RJ-45 to RJ-45

Type	Cat. No.
Cat 6	HI6XXAA*
Cat 5e	HI5EXXAA
Cat 5e, Shielded	HI5ESXXAA**

XX = Length

03 = 3'	05 = 5'	07 = 7'
10 = 10'	12 = 12'	15 = 15'
20 = 20'	25 = 25'	

* Available Q2-2004.

** Available Q3-2004.

HI-Impact™ Plugs and Cable

Call for additional product information

Type	Cat. No.
Cat 5e Plug	HI5EP
Cat 5e Patch Cable, 100'	HIPC100
F-type Connector	HIFP**
RG-59 Patch Cable, 100'	HIFC100**

** Available Q3-2004.

HI-Impact™ Cord Connectors & Grips

Call for additional product information



Cord Connectors, 0.250" - 0.375"

Description	Cat. No.
SS, 1/2"	SHC1022SSHI
Aluminum, 1/2"	SHC1022HI
Aluminum, 3/4"	SHC1032HI
Nylon, Gray, 3/4"	SHC1022CRHI

Deluxe Cord Connectors, 0.250" - 0.375"

Description	Cat. No.
SS, 1/2"	07401006HI
SS, 3/4"	07401013HI
Aluminum, 1/2"	CG406NMHI
Nylon, Gray, 1/2"	074011332HI

HI-Impact™ Enclosures

Call for additional product information



REBOX® NEMA 4/12/13, Gray

Height	Type	Cat. No.
24"	Unloaded	IR2UG
36"	Unloaded	IR3UG
48"	Unloaded	IR4UG
36"	Loaded	IR3PG
48"	Loaded	IR4PG

REBOX® NEMA 4X, Stainless Steel

Height	Type	Cat. No.
24"	Unloaded	IR2USS*
36"	Unloaded	IR3USS*

REBOX® NEMA 3R, Gray

Height	Type	Cat. No.
24"	Unloaded	IR2U2R
36"	Unloaded	IR2U3R

REBOX® Accessories

Description	Cat. No.
Plywood Backboard 20"H x 19"W	REKBB20
30"H x 19"W	REKBB30
40"H x 19"W	REKBB40
Equipment Mounting Bracket, 5U	REKZ
110/66 Block Mounting Rails (accepts five 100-pair/110-pair blocks)	REK110
Patch Panel Bracket Bottom-hinged, 4U	REK19
Fiber Patch Panel Bracket (accepts 1 FSP panel)	REKFP
Economy Power Supply Kit, 15A	REKP

DIN Rail Utility Box, Duplex

Description	Cat. No.
15A/5A Breaker	DRUBTVSS15HI
Duplex, Comm., 2-port	HIDRUBC2**
Duplex, Comm., 4-port	HIDRUBC4**

** Available Q3-2004.

Consolidation Point

Type	Size	Cat. No.
SS	NEMA 4X	HICPSS*
Gray	NEMA 4/12	HICP412G*

* Available Q2-2004.

HI-Impact™ Delivery

Call for additional product information

PolyTuff Conduit



Size	Feet	Cat. No.
1/2"	100	G1050HI
3/4"	100	G1075HI

LiquidTight, Metallic Fittings

Size	Fitting Type	Cat. No.
1/2"	Straight Male	H0501AHI
3/4"	Straight Male	H0751AHI

LiquidTight, Non-Metallic Fittings

Size	Fitting Type	Cat. No.
1/2"	Straight Male	P050NGYAH1
3/4"	Straight Male	P075NGYAH1
1/2"	SwivelLok® Male	PS0509NGYHI
3/4"	SwivelLok® Male	PS0759NGYHI

TredTrak, 5-Channel

Description	Cat. No.
Track, 3' Section	HBLTRED5BHI
End Caps	HBLTRED5ECBHI
"X" Section	HBLTRED5XBHI
"Y" Section	HBLTRED5YBHI

TrukTrak, 5-Channel

Description	Cat. No.
Track, 3' Section	HBLTT5BHI
End Caps	HBLTT5ECBHI
Right Turn	HBLTT545RBHI
Left Turn	HBLTT545LBHI



® Hubbell Premise Wiring
Hubbell Incorporated (Delaware)
1-800-626-0005
www.hubbell-premise.com

www.hubbell-solutions.com/Hi-Impact