




NPJ26GY -- Wallplates



Styleline/Rectangular Plates, 1-Gang, Mid-Sized Size, Gray Nylon

Product Specifications	
Product Type	 <p>Wall Plates</p>
Plate Material	Non-Metallic
Gangs	1
Plate Group	Styleline/Rectangular Plates
Styleline/Rectangular Plate Image- Per Gang	 <p>Styleline Opening</p>
Plate Size	Mid-Sized
Color/Material	Gray Nylon
Listings	UL Standard 514D
Certification	UL Listed E92074, CSA Certified
Thickness	.25" (6.35)
Mounting Screws	6/32" X 3/8" Oval Milled Head, Painted
Operating Temp	-40 deg. C to 85 deg. C
Appearance	Curved Corners, Smooth Finish
Product Dimensions	4.875" (123.83) X 3.125" (79.38)
UPC Number	88377810672
Weight in LBs	0.05
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

