

Product Datasheet


Catalog Home Home Page Search

# P125NBK -- Liquidtight System



P075NGYA

## Product Specifications

<b>Product Type</b>	Liquidtight System
<b>Liquidtight System Type</b>	Flexible Nonmetallic Liquidtight Connectors
<b>Liquidtight Connector Body Style</b>	Straight
<b>Trade Size</b>	1 1/4"
<b>Color</b>	 Black
<b>Effective Operating Temperature</b>	-30°F to +225°F (-34°C to +107°C).
<b>Recommended Knockout Hole Size</b>	1.72 - 1.77" (43.7 - 44.9)(mm)
<b>Flammability</b>	Nylon PolyTuff connectors have a UL 94-V2 rating, New York State Office of Fire Prevention and Control-Construction Specification Institute number 16111.
<b>Dimension A</b>	2.20" (55.9)
<b>Dimension B</b>	2.15" (54.6)
<b>Dimension C</b>	.74" (18.8)
<b>Dimension D</b>	1.30" (33.0) Throat Dia.
<b>Dimension E A/C</b>	2.38" (60.5)
<b>Dimension E A/F</b>	2.18" (55.4)
<b>Certifications</b>	UL Listed, CSA Certified
<b>UPC Number</b>	78358533396
<b>Weight in LBs</b>	0.25
<b>Link to Drawing Library</b>	<a href="#">Click here for Library</a>
<b>Link to PDF Catalog</b>	<a href="#">Click here for Catalog</a>

