

## Temporary Power Distribution Systems Portable Outlet Boxes and Plates



**HBLPOB1**



**Cover Plates**



**Deluxe Cord Grips  
(purchased separately)**



**Gray Nylon  
Cord Connector**

### Portable Outlet Boxes and Plates

Description	Catalog Numbers
Box with cord strain relief, with one blank cover plate.	<b>HBLPOB1</b>
Box with cord strain relief, with two duplex (indoor) cover plates.	<b>HBLPOB1D</b>
Blank, non-metallic FS cover plate with foam gasket, gray.	<b>HBLP14FS</b>
Duplex, non-metallic FS cover plate, gray.	<b>HBLP8FS</b>
Single receptacle (1.39"), non-metallic FS cover plate, gray.	<b>HBLP7FS</b>
Single receptacle (1.56"), non-metallic FS cover plate, gray.	<b>HBLP720FS</b>
Rectangular opening, non-metallic FS cover plate, gray.	<b>HBLP26FS</b>
<b>Other cover plates and devices which may be used with Portable Outlet Box</b>	
Duplex cover plate, weatherproof.	<b>HBL5221, HBL52CM21</b>
Single receptacle (1.39") cover plate, weatherproof.	<b>HBL7423WO, HBL74CM23WO</b>
Single receptacle (1.56") cover plate, weatherproof.	<b>HBL7425WOA, HBL74CM25WOA</b>
Safety-Shroud Twist-Lock® surface receptacles.	<b>HBL2310SR series, HBL2410SR series, HBL2610SR series, HBL2710SR series</b>

### Deluxe Cord Grips Straight Male Thread

Nylon Fittings, Stainless Steel Mesh, Liquidtight, for Insulated Cables

Grip Diameter Range Inches	(cm.)	Thread Size N.P.T. (Inches)	Form Size	Catalog Numbers
.375"-.500"	(.95-1.27)	3/4	F3	<b>074011335</b>
.500"-.625"	(1.27-1.59)	3/4	F3	<b>074011336</b>
.625"-.750"	(1.59-1.90)	3/4	F3	<b>074011337</b>

### Nylon Cord Connector Straight Male Thread

Grip Diameter Range Inches	(cm.)	Thread Size N.P.T. (Inches)	Form Size	Catalog Numbers
.375"-.500"	(.95-1.27)	3/4	F3	<b>SHC1035CR</b>
.500"-.625"	(1.27-1.59)	3/4	F3	<b>SHC1036CR</b>
.625"-.750"	(1.59-1.90)	3/4	F3	<b>SHC1037CR</b>

### Specifications

UL Listed	UL 514C, UL467 and UL 50 Enclosures Types 1, 3R, C22.2 No. 18 and C22.2 No. 94 Enclosures Types 1, 3R and C22.2 No.0.4 (Impedance).
CSA Certified	
Box Specifications:	
Moisture Resistance	Wet and damp locations, Enclosure Type 3R when used with weatherproof cover plates. Dry, indoors locations, Enclosure Type 1 with all other cover plates.
Flammability	UL 94V-0, 94-5VA classification.
Operating Temperature	80°C maximum; -35°C minimum.
UV Resistance	All materials are UV stabilized.
Impact and Crush Resistance	In accordance with UL 514C, UL50, C22.2 No. 18 and C22.2 No. 94.
Material	Valox®
Cord Connector Materials	Nylon nut; Nylon Gotcha® ring; Neoprene grommet
Cord Diameter Range	.38" to .75" diameter.
Bonding Strap Material	Brass
Threaded Inserts	Brass
Grounding Screw Material	Brass
Indoor Cover Plate Screws Material	Zinc plated steel
Outdoor Cover Plate Screws Material	Stainless steel
Cover Plate Gasket Material	UL recognized closed-cell foam (aging and oil resistant)

Valox® is a registered trademark of GE Plastics.

### Dimensions

