

Strain Relief

Deluxe Cord Grips

Nylon Fittings, Stainless Steel Mesh, Liquidtight, for Insulated Cables

**Read This Data**

It is important that you read all breaking strength, safety and technical data relating to this product on pages T-68 through T-74.

**Straight Male****90°****Straight Male Thread**

Grip Diameter Range Inches	(cm)	Thread Size N.P.T. (Inches)	Form Size	Catalog Numbers
.187"-.250"	(.47-.63)	1/2"	F2	074011331
.250"-.375"	(.63-.95)			074011332
.375"-.500"	(.95-1.27)			074011333
.500"-.625"	(1.27-1.59)			074011334*
.375"-.500"	(.95-1.27)	3/4"	F3	074011335
.500"-.625"	(1.27-1.59)			074011336
.625"-.750"	(1.59-1.90)			074011337
.750"-.875"	(1.90-2.22)			074011338*
.625"-.750"	(1.59-1.90)	1"	F4	074011341
.750"-.875"	(1.90-2.22)			074011342
.875"-.1.000"	(2.22-2.54)			074011343
1.000"-.1.125"	(2.54-2.86)			074011344*

90° Male Thread

Grip Diameter Range Inches	(cm)	Thread Size N.P.T. (Inches)	Form Size	Catalog Numbers
.250"-.375"	(.63-.95)	1/2"	F2	074011346
.375"-.500"	(.95-1.27)			074011347
.500"-.625"	(1.27-1.59)			074011348*
.375"-.500"	(.95-1.27)	3/4"	F3	074011349
.500"-.625"	(1.27-1.59)			074011350
.625"-.750"	(1.59-1.90)			074011351*

*Cable jacket may have to be stripped to pass through connector body.

