

# HBL2620SR2 -- Twist-Lock Safety-Shroud Receptacle



2P3W, 30A 250V, L6-30R, Gray 2-Gang Surface Mount Housing

## Product Specifications

### Product Type



Product Item	Single Receptacle
Wiring Scheme	2-Pole, 3-Wire Grounding
Amperage	30A
Voltage	250V AC
NEMA Configuration	L6-30R
Item Style	Shrouded
Item Version	2 Gang
Device Color	Gray
Horsepower	2
Terminal Retainer Material	Clear polycarbonate
Housing Material	Impact modified PBT
Terminal Clamp Material	Steel, nickel plated .080" Curved, scalloped
Terminal Screw Material	#10-32 Brass (white finish on neutral screw when used) Multi-drive
Ground Screw Material	#10-32 Brass (Green)
Body Contact Carrier Material	Natural White Nylon
Contact Spring Material	.031" Brass
Spring Binding Plate Material	.031" Brass
Mounting Screw Material	Brass, zinc plated
Ground Contact Material	.031" Brass
Rivet Material	Steel
Ratings	Molded In or Stamped On
Catalog No	Permanently ink marked on product
Dielectric Voltage Withstand	2,000V minimum
Current Interrupting	Certified for current interrupting at full rated current
Temperature Rise	Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.
Terminal Accommodation	30A #10 AWG
Terminal Identification	Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)
Flammability	VO or better
Operating Temperatures	Maximum Continuous 75 C Minimum -40 C (w/o impact)
Housing and Flange Material	Gray Valox 357U
Listings	FED SPEC UL/CSA
UPC Number	783585234366
Weight in LBs	0.55
Link to Drawing Library	<a href="#">Click here for Library</a>
Link to PDF Catalog	<a href="#">Click here for Catalog</a>

