



Isolated Ground Receptacles

Full Line Catalog Section 'J'

Duplex Receptacles, 15A/125V

NEMA	Color	Cat. No.
5-15R	Orange	IG5262
5-15R	Ivory	IG5262I
5-15R	Red	IG5262R
5-15R	Gray	IG5262GY



Duplex Receptacles, 20A/125V

NEMA	Color	Cat. No.
5-20R	Orange	IG5362
5-20R	Ivory	IG5362I
5-20R	Red	IG5362R
5-20R	Gray	IG5362GY

4-PLEX® Orange Receptacles

Rating	NEMA	Cat. No.
15A/125V	5-15R	IG415
20A/125V	5-20R	IG420

Surge Receptacles

Full Line Catalog Section 'J'

Surge Suppression, Straight Blade Receptacles,

125V AC/60 Hz, with Light and Alarm

	15 Amp	20 Amp
Color	Cat. No.	Cat. No.
Blue	HBL5262SA	HBL5362SA
Ivory	HBL5262ISA	HBL5362ISA
Gray	HBL5262GYSA	HBL5362GYSA
White	HBL5262WSA	HBL5362WSA
Office White	HBL5262OWSA	HBL5362OWSA



Isolated Ground, Surge Suppression Straight Blade Receptacles

125V AC/60 Hz, with Light and Alarm

	15 Amp	20 Amp
Color	Cat. No.	Cat. No.
Blue	IG5262SA	IG5362SA
Ivory	IG5262ISA	IG5362ISA
Gray	IG5262GYSA	IG5362GYSA
White	IG5262WSA	IG5362WSA
Office White	IG5262OWSA	IG5362OWSA



4-PLEX®, Surge Suppression, Straight Blade Receptacles

15A/125V AC 60 Hz

Color	Cat. No.
Blue	HBL415S
Ivory	HBL415IS



4-PLEX®, Surge Suppression, Straight Blade Receptacles

20A/125V AC 60 Hz

Color	Cat. No.
Blue	HBL420S
Ivory	HBL420IS

SpikeShield® Surge Receptacles

Full Line Catalog Section 'J'



6 Outlet 15A/125V AC Plug Strips

Application	Cat. No.
6' Surge protection, alarm, industrial grade receptacles, metal housing	HBL6PS
3' Surge protection, w/o surge status LED	HBL6PS100
6' Surge protection, w/surge status LED	HBL6PS370
6' Surge and fax/modem protection, w/surge status LED	HBL6PS370M
15' Surge protection, w/ surge status LED	HBL6PS37015



7 Outlet 15A/125V AC Plug Strips

Application	Cat. No.
6' Filtering and surge protection, w/surge status LED	HBL7PS900
6' Filtering, surge and fax/modem protection, w/surge status LED	HBL7PS900M
15' Filtering and surge protection, w/surge status LED	HBL7PS90015



8 Outlet 15A/125V AC Plug Strips

Application	Cat. No.
6' Filtering, surge and fax/modem protection, alarm, w/surge status LED	HBL8PS1380M
6' Filtering and surge protection, alarm, for CATV and DSS systems	HBL8PS1690D

SpikeShield® Panel Surge

Full Line Catalog Section 'J'



Branch Panel, Panel-Mounted, 120kA Peak Amperage

Voltage	Cat. No.
Single Phase 120/240V AC	HBL3P120
3Ø Wye 120/208V AC	HBL4P120
3Ø Delta 240V AC	HBL5P120
3Ø Delta 240/120V AC	HBL6P120
3Ø Wye 220/380V AC	HBL7P120
3Ø Wye 277/480V AC	HBL8P120
3Ø Delta 480V AC	HBL9P120
3Ø Wye 347/600V AC	HBL10P120
3Ø Delta 600V AC	HBL11P120

Branch Panel, Wired-in, 100kA Peak Amperage

Voltage	Cat. No.
Single Phase 120/240V AC	HBL3W100A
3Ø Wye 120/208V AC	HBL4W100A
3Ø Delta 240V AC	HBL5W100A
3Ø Delta 240/120V AC	HBL6W100A
3Ø Wye 220/380V AC	HBL7W100A
3Ø Wye 277/480V AC	HBL8W100A
3Ø Delta 480V AC	HBL9W100A
3Ø Wye 347/600V AC	HBL10W100A
3Ø Delta 600V AC	HBL11W100A



Branch Panel, Wired-in, 80kA Peak Amperage

Voltage	Cat. No.
Single Phase 120/240V AC	HBL3W80*
3Ø Wye 120/208V AC	HBL4W80*
3Ø Wye 220/380V AC	HBL7W80*
3Ø Wye 277/480V AC	HBL8W80*
3Ø Delta 480V AC	HBL9W80*

* Non-Metallic NEMA 4X housing

Branch Panel, Wired-in, 40kA Peak Amperage

Voltage	Cat. No.
Single Phase 120V AC	HBL1W40
Single Phase 120/240V AC	HBL3W40
Single Phase 120/240V AC	HBL3W40B*

* With back nipple

