

Product Datasheet

[Catalog Home](#)
[Home Page](#)
[Search](#)


UFC0001CR -- Underground Feeder Connectors



Gray Nylon

Hubbell's nylon cord connectors resist most common industrial corrosive and provide effective pullout protection in a lightweight design. They are ideal for any application where weight, conductivity or corrosion may be an issue.

Product Specifications

Product Type	Underground Feeder Connectors
Material/Style	Nylon
Cord Diameter Range	.2"x.4" min .25"- .55" max (5.1x10.2 min 6.3x14.0 max)
Cord Connector Body Style	Underground Feeder
HUB Size	1/2"
Color	 Gray
Recommended Knockout Hole Size	.86"- .91" (21.8-23.0)
Flammability	Hubbell nylon cord connectors have a UL 94-V2 rating.
Hazardous Locations	Hubbell cord connectors are suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C. Reference 501-4(b), 502-4(a), 502-4(b), 503-3(a), and 503-3(b).
Dimension A	1.32" (33.5) Dia.
Dimension B	1.50" (38.1) Ref.
Dimension C	.55" (14.0)
Dimension D	.58" (14.7) Throat. Dia.
Dimension E A/C	1.25" (31.7)
Dimension E A/F	1.13" (28.7)
Certifications	UL Listed in accordance with Standard 514B, CSA Certified, United States Coast Guard Approval, Title 46-Part 111.
UF Wire Size	2 # 14, 2 # 12, 2 # 10
UPC Number	78358520895
Weight in LBs	0.05
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

