
Customer Information Sheet


DRAWING No.: R40-100XX02	SHEET 2 OF 2	IF IN DOUBT - ASK	©	NOT TO SCALE	THIRD ANGLE PROJECTION	ALL DIMENSIONS IN mm

ALL SPACERS UP TO
& INCLUDING 28mm

22 TO 28mm SPACERS DO NOT HAVE A THROUGH TAPPED HOLE, BUT HAVE A MINIMUM THREAD LENGTH OF 10mm FROM BOTH ENDS.



ALL SPACERS
OVER 28mm



PART No.	L1
R40-1000502	5.00
R40-1000602	6.00
R40-1000702	7.00
R40-1000802	8.00
R40-1000902	9.00

PART No.	L1
R40-1001002	10.00
R40-1001102	11.00
R40-1001202	12.00
R40-1001302	13.00
R40-1001402	14.00

PART No.	L1
R40-1001502	15.00
R40-1001602	16.00
R40-1001802	18.00
R40-1002002	20.00
R40-1002502	25.00

PART No.	L1
R40-1002602	26.00
R40-1003002	30.00
R40-1003602	36.00
R40-1006002	60.00

ORDER CODE:
R40-100XX02
LENGTH L1 IN mm

JMB	6	15.10.06	9512
NAME	ISS.	DATE	C/NOTE

APPROVED: JB
CHECKED:
DRAWN: D BECK
CUSTOMER REF.:
ASSEMBLY DRG:

HARWiN

HARWIN INC
U.S.A.
TEL: (812) 542 2540
FAX: (812) 542 2541

HARWIN PLC
U.K.
TEL: 023 9231 4545
FAX: 023 9231 4590

HARWIN PTE
SINGAPORE
TEL: 65 6779 4909
FAX: 65 6779 3868

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
BRASS
CW614N M TO BS EN 12164
(CuZn39Pb3)

FINISH: NICKEL

S/AREA: mm²

TITLE:
M4 HEXAGONAL
FEMALE SPACER

DRAWING NUMBER:
R40-100XX02

SHT 2 OF 2