



[Sign In/Register](#)

[HOME](#) [PRODUCTS](#) [SUPPORT](#) [ABOUT US](#) [NEWS](#) [CONTACT](#)

[SEARCH](#)

[HOME](#) [Industrial Components](#) [Switches & Pilot Devices](#) [TW Series](#) [ALW29922D-R-24V](#)

**Product Families**

- [Automation](#)
- [Hazardous Location](#)
- [Industrial Components](#)
- [LED Lighting & Signaling](#)
- [Machine Safety](#)
- [Sensing](#)

## ALW29922D-R-24V 22mm Pushbutton Illuminated



**Key Features**

- Corrosion resistant octagonal chrome plated locking bezel
- Snap on 10A contacts
- Modular construction for maximum flexibility
- NEMA 4X and IP65 w atertight/oiltight panel sealing
- Available assembled or as sub-components
- UL Listed, CSA Certified, TUV Approved, and CE Marked



[Specifications](#) [Literature Downloads](#)

<b>Product Type</b>	Pushbutton Illuminated
<b>Operation Type</b>	Momentary
<b>Mounting Hole Size</b>	Φ22mm
<b>Color</b>	Red
<b>Normally Open Contacts</b>	2
<b>Normally Closed Contacts</b>	2
<b>Shape</b>	Round
<b>Illumination Voltage</b>	24V AC 24V DC