



[HOME](#)

[PRODUCTS](#)

[SUPPORT](#)

[ABOUT US](#)

[NEWS](#)

[CONTACT](#)

[USA/English](#)

[Select a country](#)

[Sign In/ Register](#)

HOME

Industrial Components

Switches & Pilot Devices

HW Series

HW4F-2F22QD-W-24V

Product Families

- Automation
- Industrial Components
- LED Lighting & Signaling
- Machine Safety
- Sensing

HW4F-2F22QD-W-24V
22mm Selector Switch Lighted



MSRP: ****

Add to Cart

Key Features

- Finger safe (IP20) screw terminals standard, other terminal styles available
- All E-Stops meet EN418 (IEC compliant, positive action)
- UL listed, CSA certified, TUV approved, and CE marked
- Super bright incandescent or LED illumination
- IP65 and NEMA type 1, 2, 3, 3R, 4, 4X, 5, 12, and 13
- 600V/10A contacts with a wide operating range from 5mA at 3V AC/DC to 10A at 120V AC



- Specifications
- Literature
- Downloads

Operation Type	Maintained
Product Type	Selector Switch Illuminated
Mounting Hole Size	Φ22mm
Shape	Round
Color	White
Normally Open Contacts	2
Normally Closed Contacts	2
Number of Positions	2
Illumination Voltage	24V AC 24V DC