



USA/English | [Select a country](#)

[Sign In/Register](#)

[HOME](#)   [PRODUCTS](#)   [SUPPORT](#)   [ABOUT US](#)   [NEWS](#)   [CONTACT](#)

Part Number Search

[HOME](#)   [Industrial Components](#)   [Switches & Pilot Devices](#)   [HW Series](#)   [HW4L-M211QD-S-24V](#)

**Product Families**

- Automation**
- Industrial Components**
- LED Lighting & Signaling**
- Machine Safety**
- Sensing**

**HW4L-M211QD-S-24V**  
22mm Pushbutton Illuminated



**MSRP:**

[Add to Cart](#)

**Key Features**

- Finger safe (IP20) screw terminals standard, other terminal styles available
- All E-Stops meet EN418 (IEC compliant, positive action)
- UL listed, CSA certified, TUV approved, and CE marked
- Super bright incandescent or LED illumination
- IP65
- 600V/10A contacts with a wide operating range from 5mA at 3V AC/DC to 10A at 120V AC



**Specifications   Literature   Downloads   Price and Availability**

<b>Operation Type</b>	Momentary
<b>Product Type</b>	Pushbutton Illuminated
<b>Mounting Hole Size</b>	φ22mm
<b>Shape</b>	Round
<b>Color</b>	Blue
<b>Normally Open Contacts</b>	1
<b>Normally Closed Contacts</b>	1
<b>Illumination Voltage</b>	24V AC 24V DC