

Product Families

- ▶ **Automation**
- ▶ **Hazardous Location**
- ▶ **Industrial Components**
- ▶ **LED Lighting & Signaling**
- ▶ **Machine Safety**
- ▶ **Sensing**

FC4A-K4A1 Analog Ouput Module 4 channels

MSRP:

[Add to Cart](#)

Key Features

- 4-pt -0-10VDC, 4-20mA
- 12 bit (0-4095) resolution



[Specifications](#) [Literature](#) [Downloads](#) [Price and Availability](#)

Product Type	Analog Exp. Module
Operating Voltage	24VDC
Output	4
Output Type	0-10VDC, 4-20mA