

Product Families

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

ALFD29901DN-G-24V 30mm Pushbutton Illuminated



Key Features

- Rugged design includes chrome plated steel locking ring and die-cast zinc threaded body
- Super bright LED or incandescent illumination
- Modular construction for maximum flexibility (up to 6 contacts per switch)
- NEMA 4X and IP65 watertight/oiltight panel seal
- Available assembled or as sub-components
- UL Listed, CSA Certified, Demko Approved, and CE Marked



Replacement: [ALFD22201DNUG](#)

Specifications

Literature

Downloads

Product Type	Pushbutton Illuminated
Operation Type	Momentary
Mounting Hole Size	Φ30mm
Color	Green
Normally Open Contacts	0
Normally Closed Contacts	1
Shape	Round
Illumination Voltage	24V AC 24V DC