

**Product Families**

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

## KIT-TOUCH-CSS FT1A Touch 14 IO Starter Kit



Add to Cart

**Key Features**

- FT1A Touch 14 I/O Type Promo Starter Kit
- Package Include: FT1A-C14SA-S, power supply, Automation Organizer software suite, and cable

**Specifications**

Product Type	Starter Kit
Input Voltage	24VDC
Input Type	Sink
Ingress Protection Rating	IP66f
Ethernet Port	1 (RJ45)
I/O Range	14
Output	4 Transistor, 2 Analog
Output Type	Transistor Source, 0-10VDC/4-20mA
I/O Expandable	Yes (up to 2 expansion cartridges)
USB Port	1 Mini B-type, 1 USB type A
Bezel Color	Silver
Screen Size	3.8 inch
Screen Type	TFT Color
Screen Resolution	240 x 100 pixels
Color Depth	65,536 colors
Brightness	400 cd/m2
Built In Memory	Ladder: 48KB, HMI: 5MB
Communication Ports	USB Mini-B, USB Type A, Ethernet, RS232C/422/485
Input Channels	8