

Product Families

- ▶ [Automation](#)
- ▶ [Hazardous Location](#)
- ▶ [Industrial Components](#)
- ▶ [LED Lighting & Signaling](#)
- ▶ [Machine Safety](#)
- ▶ [Sensing](#)

ARNS1-1010-10.00.10.00 2Pos Monolever

[Add to Cart](#)

Key Features

- Up to four positions
- Maintained or spring return in any combination
- 3 styles including an interlocking lever
- Contacts rated for 10A / 600V
- UL Listed, CSA Certified



No Image Available



[Specifications](#)