

HOME > Industrial Components > Relays And Sockets > RV8H Series > SV9Z-SAW

Product Families

- > Automation
- > Sensing
- > LED Lighting & Signaling
- > Machine Safety
- > Industrial Components
 - > Switches & Pilot Devices
 - > Circuit Breakers
 - > Power Supplies
 - > Relays And Sockets
 - > RV8H Series
 - > RJ Series
 - > RJ Bifurcated Series
 - > RU Series
 - > RH Series
 - > RR Series
 - > RY-RM Series
 - > RJ PCB Series
 - > RQ Series
 - > RR2KP Series
 - > RY2KS Series
 - > RF1V Series
 - > Solid State Relays
 - > Timers
 - > IEC Contactors
 - > Terminal Blocks

SV9Z-SAW
Spacer Gray for RV



MSRP: ****

Add to Cart

Key Features

- Space-saving 6mm width
- Only 70mm in height from DIN rail
- Gold-plated contacts
- Pre-assembled relay and DIN mount socket
- Universal screw terminals (flat and Phillips)
- Universal AC/DC socket with built-in surge suppression and green LED
- Lever for easy locking and removal of relay
- Wide input voltage range: 6 to 240V
- High dielectric strength and impulse withstand voltages
- Reverse Polarity protected
- 400V AC maximum switching voltage
- Spring clamp accepts 20-14 AWG solid or stranded wires
- 1500VA maximum switching power
- RoHS compliant

Specifications

Literature

Downloads

Product Type	Accessories Marking plate (16 pcs)
Compatible IDEC Device	RV series