

Product Families

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

ASD3322N
30mm Selector Switch



Key Features

- Rugged design includes chrome plated steel locking ring and die-cast zinc threaded body
- Super bright LED or incandescent illumination
- Modular construction for maximum flexibility (up to 6 contacts per switch)
- NEMA 4X and IP65 watertight/oiltight panel seal
- Available assembled or as sub-components
- UL Listed, CSA Certified, Demko Approved, and CE Marked



Replacement: [ASD3322NU](#)

Specifications

Literature

Downloads

Product Type	Selector Switch
Operation Type	Spring Return from Left and Right to Center
Mounting Hole Size	Φ30mm
Normally Open Contacts	2
Normally Closed Contacts	2
Shape	Round
Number of Positions	3