

Product Families

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

HN1E-BV4F11-R
30mm Emergency-Stop



Add to Cart

Key Features

- Rugged design includes chrome plated steel locking ring and die-cast zinc threaded body
- Super bright LED or incandescent illumination
- Modular construction for maximum flexibility (up to 6 contacts per switch)
- NEMA 4X and IP65 watertight/oiltight panel seal
- Available assembled or as sub-components
- UL Listed, CSA Certified, Demko Approved, and CE Marked



Specifications

Literature

Downloads

Product Type	Emergency-Stop
Operation Type	Push Lock - Turn Reset
Mounting Hole Size	Φ30mm
Color	Red
Normally Open Contacts	1
Normally Closed Contacts	1