

Product Families

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

ASLD33222DNU-310-R
30mm 3pos S2W 24V 2NO2NC Red

Add to Cart

Key Features

- Diecast zinc mounting threads
- Heavy-duty design for all type of harsh environments
- IP20 finger-safe contact block
- Ease of installation and wiring
- UL Listed, CSA Certified, TUV Approved, and CE Marked



Specifications Literature Downloads

Operation Type	Spring return
Mounting Hole Size	30mm
Color	Red (R)
Shape	Knob
Number of Positions	3
Contact Configuration	2NO 2NC
Rated Voltage	24V AC/DC
Terminal Type	Screw (M3.5)
Ingress Protection Rating	IP65
Operator Position Angle	45 deg.