

Product Families

- ▶ Automation
- ▶ Hazardous Location
- ▶ Industrial Components
- ▶ LED Lighting & Signaling
- ▶ Machine Safety
- ▶ Sensing

HS5E-D4401-G
Safety Switch Spring Lock



Key Features

- World's smallest 4 contact solenoid interlock switch. (35 x 40 x 146 mm)
- Flexible installation - the head can rotate, allowing 8 different actuator entries
- Metal actuator entry slot ensures long life
- Standard 3m cable (1m and 5m cable available on request)
- Only proprietary actuators can be used, preventing unauthorized access (ISO14119, EN1088)
- 1000N min actuator locking strength (GS-ET-19)
- LED pilot light indicates the solenoid status
- Gold-plated contacts
- NC contacts are direct opening (IEC/EN60947-5-1)
- IP67 (IEC60529)
- B10d: 2.0E+06

Replacement: [HSSL-VD44M-G](#)

Specifications Literature Downloads Related

Product Type	Locking Solenoid Safety Switch
Lock Method (actuator inserted)	Spring Lock
Unlock Method	Energize Solenoid
Solenoid Voltage	24V DC
Indicator Light	Green
Main Contacts	1NC+1NC
Actuator Monitor Contacts	1NC
Solenoid Monitor Contacts	1NC
Cable Length	1 m
Retention Force	1,000N
B10d (cycle)	2.00E+06