



[Home](#) / [Products](#) / Search Result

4-in-1 Test Tool

Products

- [Wire Termination](#)
- [Test & Measurement](#)
- [DataComm](#)
- [Tools & Totes](#)
- [Wire Management](#)
- [Wire Installation](#)
- [Mil-Aero Wire Processing](#)
- [OEM Connection Systems](#)
- [Electrical Supplies](#)



Product Resources

- [Basics of Digital Multimeters](#)
(PDF | 914K)
- [61-702, 61-704 200 AAC Clamp Meter Instructions](#)
(PDF | 232K | Rev 3)
- [61-700, 61-701, 61-702 & 61-704 Manual](#)
(PDF | 232K | Rev 4)

Features

- True RMS
- Non-contact voltage
- Backlight
- CAT III - 1000V
- 200A Current capability
- Audible continuity
- Diode Test
- Data hold/max hold
- Low battery indicator
- Overload protection on all ranges
- Silicone leads
- Sleep mode
- Compact head design
- Includes carrying case
- 2-year warranty

Models

Description	Catalog #
4-in-1 Test Tool	61-704

Follow Us:

