



fl

FIND DISTRIBUTOR

OUR COMPANY
PRODUCTS
DOWNLOADS
KNOWLEDGE BASE
CONTACT

ALL
PASTE
LIQUID SOLDER FLUX
TACKY SOLDER FLUX
SOLDER WIRE
BAR SOLDER
OTHER

44 FLUX-CORED WIRE



Kester 44 Rosin Flux is an activated rosin formula for use in flux-cored solder wire. Kester 44 Rosin Flux has virtually dominated the field of activated rosin core solders for well over four decades. An outstanding performance feature of this flux is the "instant-action" wetting behavior. The high mobility and fast-spreading action of this flux results in more reliable production line soldering.

[SHARE](#)

FIND A DISTRIBUTOR TO BUY

DOWNLOADS

- [Data Sheet](#) >
- [Lead Alloy SDS](#) >
- [Lead-Free Alloy SDS](#) >
- [SDS \(MSDS\) Spanish](#) >

PRODUCT OFFERINGS

[DOWNLOAD FULL SPREADSHEET](#) | [DOWNLOAD CURRENT TABLE](#)

ALLOY	FLUX	DIAMETER	CORE	LEAD FREE	DESCRIPTION	PART #
All	All	All	All	All		
AG03PB97	44	0.062	50	No	AG03PB97 #50/44 .062 5 LB SPL	2674000059
SAC305	44	0.02	66	Yes	SN96.5AG03CU.5 #66/44 .020 1 LB SPL	2470680010
SAC305	44	0.031	66	Yes	SN96.5AG03CU.5 #66/44 .031 1 LB SPL	2470680027
SAC305	44	0.04	66	Yes	SN96.5AG03CU.5 #66/44 .040 1 LB SPL	2470680039
SAC305	44	0.062	58	Yes	SN96.5AG03CU.5 #58/44 .062 18 LB SPL	2770680060
SN01PB97.5AG1.5	44	0.025	58	No	SN01PB97.5AG1.5 #58/44 .025 1 LB SPL	2400150017
SN40PB60	44	0.062	66	No	SN40PB60 #66/44 .062 1 LB SPL	2440600061
SN40PB60	44	0.093	66	No	SN40PB60 #66/44 .093 1 LB SPL	2440600066
SN40PB60	44	0.093	66	No	SN40PB60 #66/44 .093 5 LB SPL	2640600066
SN40PB60	44	0.25	66	No	SN40PB60 #66/44 .250 EZD	2940600177
SN50PB50	44	0.062	66	No	SN50PB50 #66/44 .062 1 LB SPL	2450500061
SN50PB50	44	0.062	66	No	SN50PB50 #66/44 .062 5 LB SPL	2650500061
SN50PB50	44	0.093	66	No	SN50PB50 #66/44 .093 1 LB SPL	2450500066
SN50PB50	44	0.125	58	No	SN50PB50 #58/44 .125 1 LB SPL	2450500068
SN50PB50	44	0.125	66	No	SN50PB50 #66/44 .125 1 LB SPL	2450500069
SN5PB93.5AG1.5	44	0.01	58	No	SN05PB93.5AG1.5 #58/44 .010 1 LB SPL	2473400000
SN5PB93.5AG1.5	44	0.015	58	No	SN05PB93.5AG1.5 #58/44 .015 1 LB SPL	2473400006
SN5PB93.5AG1.5	44	0.031	58	No	SN05PB93.5AG01.5 #58/44 .031 1 LB SPL	2473400026
SN5PB93.5AG1.5	44	0.062	58	No	SN05PB93.5AG01.5 #58/44 .062 1 LB SPL	2473400060

SN60PB40	44	0.015	66	No	SN60PB40 #66/44 .015 1 LB SPL	2460400007
SN60PB40	44	0.02	66	No	SN60PB40 #66/44 .020 1 LB SPL	2460400010
SN60PB40	44	0.025	58	No	SN60PB40 #58/44 .025 1 LB SPL	2460400017
SN60PB40	44	0.025	66	No	SN60PB40 #66/44 .025 1 LB SPL	2460400018
SN60PB40	44	0.031	58	No	SN60PB40 #58/44 .031 1 LB SPL	2460400026
SN60PB40	44	0.031	66	No	SN60PB40 #66/44 .031 1 LB SPL	2460400027
SN60PB40	44	0.04	58	No	SN60PB40 #58/44 .040 1 LB SPL	2460400038
SN60PB40	44	0.04	58	No	SN60PB40 #58/44 .040 5 LB SPL	2660400038
SN60PB40	44	0.04	66	No	SN60PB40 #66/44 .040 1 LB SPL	2460400039
SN60PB40	44	0.04	66	No	SN60PB40 #66/44 .040 5 LB SPL	2660400039
SN60PB40	44	0.05	58	No	SN60PB40 #58/44 .050 1 LB SPL	2460400052
SN60PB40	44	0.05	66	No	SN60PB40 #66/44 .050 1 LB SPL	2460400053
SN60PB40	44	0.05	66	No	SN60PB40 #66/44 .050 20 LB SPL	2860400053
SN60PB40	44	0.062	58	No	SN60PB40 #58/44 .062 1 LB SPL	2460400060
SN60PB40	44	0.062	66	No	SN60PB40 #66/44 .062 1 LB SPL	2460400061
SN60PB40	44	0.062	66	No	SN60PB40 #66/44 .062 5 LB SPL	2660400061
SN60PB40	44	0.062	66	No	SN60PB40 #66/44 .062 20 LB SPL	2860400061
SN60PB40	44	0.081	66	No	SN60PB40 #66/44 .081 5 LB SPL	2660400103
SN60PB40	44	0.093	66	No	SN60PB40 #66/44 .093 1 LB SPL	2460400066
SN60PB40	44	0.125	58	No	SN60PB40 #58/44 .125 5 LB SPL	2660400068
SN60PB40	44	0.125	66	No	SN60PB40 #66/44 .125 1 LB SPL	2460400069
SN60PB40	44	0.125	66	No	SN60PB40 #66/44 .125 5 LB SPL	2660400069
SN62PB36AG2	44	0.02	58	No	SN62PB36AG02 #58/44 .020 1 LB SPL	2471500009
SN62PB36AG2	44	0.02	66	No	SN62PB36AG02 #66/44 .020 1 LB SPL	2471500010
SN62PB36AG2	44	0.025	66	No	SN62PB36AG02 #66/44 .025 1 LB SPL	2471500018
SN62PB36AG2	44	0.031	66	No	SN62PB36AG02 #66/44 .031 1 LB SPL	2471500027
SN62PB36AG2	44	0.05	66	No	SN62PB36AG02 #66/44 .050 1 LB SPL	2471500053
SN62PB36AG2	44	0.062	58	No	SN62PB36AG02 #58/44 .062 5 LB SPL	2671500060
SN63PB36.65SB.35	44	0.02	66	No	SN63PB36.65SB.35 #66/44 .020 1 LB SPL	2400630010
SN63PB37	44	0.01	66	No	SN63PB37 #66/44 .010 1 LB SPL	2463370001
SN63PB37	44	0.015	66	No	SN63PB37 #66/44 .015 1 LB SPL	2463370007
SN63PB37	44	0.02	58	No	SN63PB37 #58/44 .020 1 LB SPL	2463370009
SN63PB37	44	0.02	66	No	SN63PB37 #66/44 .020 1 LB SPL	2463370010
SN63PB37	44	0.025	58	No	SN63PB37 #58/44 .025 1 LB SPL	2463370017

SN63PB37	44	0.025	66	No	SN63PB37 #66/44 .025 1 LB SPL	2463370018
SN63PB37	44	0.031	58	No	SN63PB37 #58/44 .031 1 LB SPL	2463370026
SN63PB37	44	0.031	66	No	SN63PB37 #66/44 .031 1 LB SPL	2463370027
SN63PB37	44	0.04	58	No	SN63PB37 #58/44 .040 5 LB SPL	2663370038
SN63PB37	44	0.04	66	No	SN63PB37 #66/44 .040 1 LB SPL	2463370039
SN63PB37	44	0.05	66	No	SN63PB37 #66/44 .050 1 LB SPL	2463370053
SN63PB37	44	0.062	58	No	SN63PB37 #58/44 .062 1 LB SPL	2463370060
SN63PB37	44	0.062	66	No	SN63PB37 #66/44 .062 1 LB SPL	2463370061
SN63PB37	44	0.125	66	No	SN63PB37 #66/44 .125 1 LB SPL	2463370069
SN95AG5	44	0.02	66	Yes	SN95AG05 #66/44 .020 1 LB SPL	2470700010
SN95AG5	44	0.031	50	Yes	SN95AG05 #50/44 .031 1 LB SPL	2470700025
SN95AG5	44	0.031	66	Yes	SN95AG05 #66/44 .031 1 LB SPL	2470700027
SN95AG5	44	0.032	58	Yes	SN95AG05 #58/44 .032 1 LB SPL	2470700029
SN95AG5	44	0.062	58	Yes	SN95AG05 #58/44 .062 1 LB SPL	2470700060
SN95AG5	44	0.062	66	Yes	SN95AG05 #66/44 .062 1 LB SPL	2470700061
SN95SB5	44	0.025	66	Yes	SN95SB05 #66/44 .025 1 LB SPL	2470800018
SN95SB5	44	0.031	50	Yes	SN95SB05 #50/44 .031 4 LB SPL	2570800025
SN95SB5	44	0.031	66	No	SN95SB05 #66/44 .031 1 LB SPL	2400010027
SN95SB5	44	0.031	66	Yes	SN95SB05 #66/44 .031 1 LB SPL	2470800027
SN95SB5	44	0.031	66	Yes	SN95SB05 #66/44 .031 4 LB SPL	2570800027
SN95SB5	44	0.062	58	Yes	SN95SB05 #58/44 .062 1 LB SPL	2470800060
SN95SB5	44	0.062	66	Yes	SN95SB05 #66/44 .062 1 LB SPL	2470800061
SN96.3AG3.7	245	0.02	66	Yes	SN96.3AG3.7 #66/245 .020 1 LB SPL	2470508808
SN96.3AG3.7	245	0.031	50	Yes	SN96.3AG3.7 #50/245 .031 1 LB SPL	2470508800
SN96.3AG3.7	245	0.04	50	Yes	SN96.3AG3.7 #50/245 .040 1 LB SPL	2470508813
SN96.3AG3.7	245	0.04	58	Yes	SN96.3AG3.7 #58/245 .040 1 LB SPL	2470508846
SN96.3AG3.7	44	0.015	66	Yes	SN96.3AG3.7 #66/44 .015 1 LB SPL	2470500007
SN96.3AG3.7	44	0.02	66	Yes	SN96.3AG3.7 #66/44 .020 1 LB SPL	2470500010
SN96.3AG3.7	44	0.031	66	Yes	SN96.3AG3.7 #66/44 .031 1 LB SPL	2470500027
SN96.3AG3.7	44	0.031	70	Yes	SN96.3AG3.7 #70/44 .031 1 LB SPL	2400960075
SN96.3AG3.7	44	0.04	66	Yes	SN96.3AG3.7 #66/44 .040 1 LB SPL	2470500039
SN96.3AG3.7	44	0.062	66	Yes	SN96.3AG3.7 #66/44 .062 1 LB SPL	2470500061
SN96.3AG3.7	44	0.093	66	Yes	SN96.3AG3.7 #66/44 .093 1 LB SPL	2470500066
SN96.5AG3.5	44	0.02	58	Yes	SN96.5AG03.5 #58/44 .020 1 LB SPL	2470400009

SN96.5AG3.5	44	0.031	58	Yes	SN96.5AG03.5 #58/44 .031 1 LB SPL	2470400026
SN96.5AG3.5	44	0.031	66	Yes	SN96.5AG03.5 #66/44 .031 1 LB SPL	2470400027
SN96.5AG3.5	44	0.062	66	Yes	SN96.5AG03.5 #66/44 .062 4 LB SPL	2570400061
SN96.5AG3.5	44	0.062	66	Yes	SN96.5AG03.5 #66/44 .062 1 LB SPL	2470400061
SN97AG.2SB.8CU2	44	0.031	66	Yes	SN97AG.20SB.80CU2 #66/44 .031 1 LB SPL	2470310027
SN99	44	0.04	58	Yes	SN99 #58/44 .040 4 LB SPL	2570000038
SN99	44	0.062	50	Yes	SN99 #50/44 .062 4 LB SPL	2570000059
SN99	44	0.093	58	Yes	SN99 #58/44 .093 4 LB SPL	2570000065
SN99.3CU.7	44	0.062	66	Yes	SN99.3CU.7 #66/44 .062 1 LB SPL	2470120061

PROCESS COMPATIBLE PRODUCTS

186 SOLDERING FLUX



- [VIEW PRODUCT](#)
- [DATA SHEET](#)
- [SDS](#)



OVERVIEW
CORPORATE CITIZENSHIP
EMPLOYMENT

PASTE
LIQUID SOLDER FLUX
TACKY SOLDER FLUX
BAR SOLDER
SOLDER WIRE
OTHER

SDS
ENVIRONMENTAL
DATA SHEETS
CATALOGS

FAQ
ALLOY PROPERTIES
LEAD-FREE SOLUTIONS

DISTRIBUTION
SALES
CUSTOMER SERVICE

[FIND DISTRIBUTOR](#)

Search Kester.com