




NOTES:
 1. FOR USE WITH RG-122/180/195 AMPHENOL 21-597 &
 RAYCHEM 09-026 CABLE GROUPS.

HEX SIZES (ACROSS FLATS)				DIE WIDTH	WEB WIDTH		
A	B	C	D	F	G	H	I
.069	—	.178	—	.400	.080	—	—

UNLESS OTHERWISE SPECIFIED:
 1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS $\pm .010$
 3 PLACE DECIMALS $\pm .004$
 T.I.R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES.
 2. REMOVE ALL BURRS. BREAK SHARP EDGES .005 MAX.
 3. NO FILLETS PERMITTED.
 4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
 5. ALL DIMENSIONS PRIOR TO PLATING.

REVISION	
ISSUE	CHANGES
2	CN 27545 C SD 7NOV85

DRAWN JGL.		DATE 15 JUN 72	
APPR.		DATE	
KING ELECTRONICS 40 MARBLEDALE ROAD TUCKAHOE, N. Y. 10707			
KTH-2007			