



Tool Online Catalog

WHERE TO BUY

Select a Category

GO

ADJUSTABLE WRENCHES - STANDARD CAPACITY

[Product Index](#) > [Wrenches](#) > [Adjustable Wrenches](#) > [Adjustable Wrenches - Standard Capacity](#) > 506-12

12" Adjustable Wrench — Standard Capacity

- Forged heat-treated alloy steel for maximum strength and light weight.
- High polish chrome finish.



Buy Now!

Pictured: 506-8

Cat. No.	Capacity	Handle Finish	Handle Type	Length	Weight (lbs.)
506-12	1-5/16" (33)	plain	dovetail	12-1/4" (311)	1.32

All dimensions are in inches and (millimeters) except where indicated.

Download High-Resolution .jpg photo

Download High-Resolution .eps photo



The downloadable files are compressed in .zip format to save on downloading times.
Decompressing .zip files requires applications such as [WinZip](#) for the PC and [Stuffit Expander](#) for the Macintosh.

 **WARNINGS:** Always wear approved eye protection.

 **WARNINGS:** Do NOT push or hammer wrench.

 **WARNINGS:** Do NOT extend handle length.

For questions regarding Klein Tools, please use the [Contact Klein Tools](#) page. For questions regarding Klein Tools' policy regarding the use of this site, please see our [Legal Notice/Privacy Statement](#).