




Ship Auger Bit with Screw Point 3/4-Inch



The deep, open-throat design of the Ship Auger bit clears chips for faster, cleaner cuts. The shank is 7/16-Inch hex to fit 1/2-Inch (13 mm) and larger three-jaw chucks. Used for heavy construction and repair work in mines, on docks and bridges as well as electrical work.

Specifications

Bit Diameter:	3/4" (19 mm)	Shank Diameter:	0.4"
Twist Length:	4" (10.2 cm)	Overall Length:	6" (15.2 cm)
Weight:	6.4 oz (181 g)		