



Tool Online Catalog

WHERE TO BUY

Select a Category

GO

UNIBIT® HIGH SPEED STEEL STEP-DRILL BITS - INCH

[Product Index](#) > [Drill Bits and Hole Saws](#) > [Step-Drill Bits](#) > [Unibit® High Speed Steel Step-Drill Bits - Inch](#) > 59003

Unibit® High-Speed Steel Step-Drill Bit — Inch

- Single-fluted design eliminates skidding and makes for easier resharpening.
- Laser-etched hole sizes are easy-to-read and permanent.
- Anti-skid tip eliminates the need for center punching or pilot hole drilling for most sizes.
- Drill multiple-size holes in thin sections of metal, plastic, and wood using a single bit.
- Works in most metals (steel, brass, aluminum, copper), as well as in plastic and wood.
- Note: Read and follow safety instructions in power tool owner's manual.



Buy Now!

Pictured: 59003

Cat. No.	Depth penetration for each step	Electric drill size	Number of Hole Sizes per Bit	Pilot hole required	Quick Reference No.	Size Range (Hole Diameter)	Weight (lbs.)
59003	1/8"	3/8" and larger	9 in 1/16" increments	no	3	1/4" to 3/4"	.15

All dimensions are in inches and (millimeters) except where indicated.

Download High-Resolution .jpg photo

Download High-Resolution .jpg lineart

Download High-Resolution .eps photo

Download High-Resolution .eps lineart



The downloadable files are compressed in .zip format to save on downloading times.

Decompressing .zip files requires applications such as [WinZip](#) for the PC and [Stuffit Expander](#) for the Macintosh.

 WARNINGS: Always ensure that you and persons in the vicinity wear approved eye protection.

 WARNINGS: Never use on or near live electrical circuits.

For questions regarding Klein Tools, please use the [Contact Klein Tools](#) page. For questions regarding Klein Tools' policy regarding the use of this site, please see our [Legal Notice/Privacy Statement](#).