



Select a Category

GO

CURVED LONG NEEDLE-NOSE PLIERS - EXTRA-SLIM

[Product Index](#) > [Pliers](#) > [Long-Nose Pliers](#) > [Curved Long Needle-Nose Pliers - Extra-Slim](#) > [D338-51/2C](#)

5" Curved Long Needle-Nose Pliers - Extra Slim

- 60° bent nose for maximum work visibility in confined areas.
- Easily bends and forms fine wire.
- Polished inside jaws and radiused jaw edges prevent nicking wire.
- Spring-loaded for self-opening action
- Curved handles provide greater tool control.



Buy Now!

Pictured: D338-51/2C

Cat. No.	Handle Color	Handle Finish	Jaw Length	Jaw Thickness	Jaw Width	Overall Length	Point Thickness	Weight (lbs.)
D338-51/2C	dark blue	plastic-dipped	1-1/2" (38)	5/16" (8)	1/2" (13)	5-1/2" (140)	1/16" (1.6)	.14

All dimensions are in inches and (millimeters) except where indicated.

[Download High-Resolution .jpg photo](#)

[Download High-Resolution .eps photo](#)



The downloadable files are compressed in .zip format to save on downloading times. Decompressing .zip files requires applications such as [WinZip](#) for the PC and [Stuffit Expander](#) for the Macintosh.

⚠ WARNINGS: Always wear approved eye protection.

⚠ WARNINGS: NOT insulated. Plastic-dipped or slip-on plastic handles are NOT intended for protection against electrical shock.

For questions regarding Klein Tools, please use the [Contact Klein Tools](#) page. For questions regarding Klein Tools' policy regarding the use of this site, please see our [Legal Notice/Privacy Statement](#).