

Double Row Terminal Blocks

Kulka® 604 GP Series

600 Volts



Specifications:

- Base, General Purpose Phenolic, 150°C
- JJ (GDI-30F) Material Available
- Open Back Design (Insulator Strip Required for Voltage Rating)
- Screws, #12-32 Binder Head, Phil-Slot, Brass
- Terminals, Plated Brass
- 1-8 Poles
- 7/8" Centers
- Wire Range With Wire Binding Screw #4-#12 AWG – 70 Amps
- The Suitability Of These Devices For Greater Currents Shall Be Determined In The End-Use Application
- UL Recognized File No. XCFR2.E47811
- CSA Certified File No. LR19766
- CE

Catalog #	# of poles	Dimensions	
		A	B
604 GP 01 PSB	1	2.28	1.75
604 GP 02 PSB	2	3.16	2.63
604 GP 03 PSB	3	4.03	3.50
604 GP 04 PSB	4	4.91	4.38
604 GP 05 PSB	5	5.78	5.25
604 GP 06 PSB	6	6.66	6.13
604 GP 07 PSB	7	7.53	7.00
604 GP 08 PSB	8	8.41	7.88

MM = Dim X 25.4

Hardware Options: (Hardware options may affect ratings - consult factory)

2402 = Stud 10 - 32 Brass (.43 H) Nuts Included See Page 103
 J 604 = Line to Line Jumper See Page 101

See pages 96-111 for terminal block accessories

