

## 672 GP Series (300 Series) - Double Row Terminal Blocks



672 GP 03

### Specifications

- A Kulka® Brand
- 30 amps
- 600 Volts AC/DC, Class C
- Base, phenolic, 150°C (UL RTI)
- Screws, steel, #8-32 phil-slot
- Terminals, plated brass
- Closed back
- 1-24 poles at 9/16" centers
- Accepts lugs w/max width of .42"
- Bare wire range #10-#14 AWG

### Standards

- UL recognized file no. XCFR2.E62806
- CSA certified file no. LR19766
- CE Compliant (IEC 60947-7-1)
- RoHS compliant

### Double Row Terminal Blocks - 672 GP Series (300 Series)

Catalog #	Alternate Catalog #	# of Poles	Dimensions	
			A	B
672 GP 01	301	1	1.54	1.13
672 GP 02	302	2	2.10	1.69
672 GP 03	303	3	2.66	2.25
672 GP 04	304	4	3.22	2.81
672 GP 05	305	5	3.79	3.38
672 GP 06	306	6	4.35	3.94
672 GP 07	307	7	4.91	4.50
672 GP 08	308	8	5.47	5.06
672 GP 09	309	9	6.04	5.63
672 GP 10	310	10	6.60	6.19
672 GP 11	311	11	7.16	6.75
672 GP 12	312	12	7.72	7.31
672 GP 13	313	13	8.29	7.88
672 GP 14	314	14	8.85	8.44
672 GP 15	315	15	9.41	9.00
672 GP 16	316	16	9.97	9.56
672 GP 17	317	17	10.54	10.13
672 GP 18	318	18	11.10	10.69
672 GP 19	319	19	11.66	11.25
672 GP 20	320	20	12.22	11.81
672 GP 21	321	21	12.79	12.38
672 GP 22	322	22	13.35	12.94
672 GP 23	323	23	13.91	13.50
672 GP 24	324	24	14.47	14.06

mm = dim X 25.4

### Hardware Options

(Hardware options may affect ratings - Consult Customer Service)

Catalog #	Product Description	Reference Sheet
KT55	Full Quick Connect (0 degree Flat)	Reference
KT56	Full Quick Connect (45 degree Bend)	
KT57	Full Quick Connect (90 degree Bend)	
KT61	Half Quick Connect (0 degree Flat)	
KT62	Half Quick Connect (45 degree Flat)	
KT63	Half Quick Connect (90 degree Flat)	
ST	Full Solder	Reference
3/4 ST	Half Solder	
J 602	Line-to-Line Jumper	Reference
3786	SEMS Pressure Saddle Screw*	Reference
SPSE	SEMS Pressure Saddle Screw with external tooth lock washer*	
PSB	Phil-Slot Brass Screw	Add "PSB" after part number
	Covers - Top-Mounted	Reference
	Marking & Insulator Strips - Sub-Mounted	Reference
	Marking Strips - Top-Mounted	Reference

Quick Connects: .032" x .250"

\*Bare wire range with SEMS screw of #10-22 AWG, stranded copper wire only

### CONTACT

Marathon Special Products  
427 Van Camp Road  
P.O. Box 468  
Bowling Green, Ohio 43402

tel: 419-352-8441  
fax: 419-352-0875  
email: [marketing@marathonsp.com](mailto:marketing@marathonsp.com)

### CUSTOMER SERVICE HOURS

Mon-Fri 8am-5pm EST

### LINKS

- [About Us](#)
- [Contact Us](#)
- [Terms & Conditions](#)
- [Locate a Distributor](#)

### ABOUT

Marathon Special Products is an industry leader for supplying power blocks, terminal blocks, and fuse holders in North America. We've achieved this by providing one of the broadest line offerings with various sizes, terminal styles, electrical ratings and features.



