


LTR	REVISION	DATE	APPD
A	010320-HF02: ADDED P/N's: PP156TR4-0002, PP156TG4-014V-W6 & PP156TY4-14V-W6	01-03-20	HF



**NOTES:**

1. ALL DIMENSIONS ARE IN INCHES [MILLIMETERS].
2. SLEEVE MATERIAL / COLOR: NYLON 66 UL94V-0 / BLACK
3. MOUNTING DIAMETER: Ø5/32"

**ELECTRICAL-OPTICAL CHARACTERISTICS (Ta = 25°C)**

REVISION NOTIFICATION	
<input type="checkbox"/> DLC	
<input type="checkbox"/> UL/ETL	
<input type="checkbox"/> MADE IN USA	
<input type="checkbox"/> CUSTOMER _____	
<input type="checkbox"/> OTHER	
REDLINE CHECKLIST	
<input type="checkbox"/> REDLINE(YES)	
<input type="checkbox"/> DATE: _____	
<input type="checkbox"/> INITIATED BY: _____	
<input type="checkbox"/> ECR REQUIRED YES <input type="checkbox"/> NO <input type="checkbox"/>	
<input type="checkbox"/> WORK ORDER# _____	

LEDTRONICS PART NO.	COLOR EMITTED	INPUT VOLTAGE, V (Tested@14Vdc)	CURRENT (A)	POWER (W)	MAXIMUM CANDELA	λ.P nm COLOR TEMP. (K)	VIEWING ANGLE (FULL BEAM WIDTH @ 50% INTENSITY)
PP156TR4-0002	HI-EFF RED	12/14Vdc	0.013 A	0.18 W	0.016 cd	642	55°
PP156TG4-014V-W6	HI-EFF GREEN	12/14Vdc	0.015 A	0.21 W	-	562	45°
PP156TY4-14V-W6	YELLOW	12/14Vdc	0.015 A	0.21 W	0.012 cd	585	45°

**LED<sup>®</sup>**  
**LEDTRONICS,™ INC.**  
 23105 KASHIWA COURT  
 TORRANCE, CA 90505

**-PROPRIETARY-**  
 This document contains Proprietary information of LEDTRONICS, INC. It may not be copied, used or disclosed for any purpose without the prior express written consent of LEDTRONICS, INC.

.XXX ± .010 TOLERANCE PER ANSI-Y14.5  
 .XX ± .025 (UNLESS OTHERWISE STATED)  
 ANGLES ± 0°,30'  
 FRACT. ± 1/32

TITLE							
PP156TR4-0002 PP156-XXX-014V-W6							
DWG NO	SCALE	SHEET	DATE				
PP156-14V-W6	NTS	1 OF 1	08-30-11				
CODE IDENT NO.	DWG BY	CHK BY	QA	SB	MFG LD	R&D UF	
8Z410	08-30-11		01-10-20	01-10-20	01-10-20	01-10-20	