

- [About Leviton](#)
- [A Century of Success](#)
- [Press](#)
- [Join Our eMailing List](#)
- [Trade Shows](#)
- [RoHS](#)
- [Career Opportunities](#)
- [Contact Us](#)
- [All Leviton Products](#)
- [Electrical](#)
- [Network Solutions](#)
- [Lighting Controls](#)
- [Entertainment](#)
- [Home Automation](#)
- [Connected Home](#)
- [Energy Management](#)
- [Power Quality](#)
- [Library Home](#)
- [Application Notes](#)
- [Brochures / Catalogs](#)
- [Case Studies](#)
- [DDLs](#)
- [Downloads](#)
- [Drawings](#)
- [Line Cards](#)
- [Manuals / Instructions](#)
- [Product Specifications / Datasheets](#)
- [Software](#)
- [Specs \(AIA / CSI\)](#)
- [Take One](#)
- [Tech Notes](#)
- [Technical Articles](#)
- [Videos](#)
- [ez-Biz](#)
- [ez-Find](#)
- [ez-Learn](#)
- [ez-Configurator](#)
- [Distribution Home](#)
- [Contractor Connection](#)
- [ez-Learn](#)
- [ez-Find](#)
- [Sign In - B2B](#)
- [OEM Home](#)
- [How to Buy](#)
- [Whats New](#)
- [Press/News](#)
- [Retail Home](#)
- [Product Information](#)
- [How To](#)
- [Merchandising](#)
- [Energy Smart Living](#)
- [International Home](#)
- [China \(English\)](#)
- [China \(Chinese\)](#)
- [Mexico \(English\)](#)
- [Mexico \(Spanish\)](#)
- [Middle East \(English\)](#)
- [International Contact](#)
- [Press](#)
- [Products](#)
- [Trade Shows](#)
- [Made to Order](#)
- [EZE-Rough](#)
- [Acenti Devices](#)
- [AC Switches](#)
- [Appliance Switches](#)
- [Architectural Controls](#)
- [Camera Systems](#)
- [Combination Devices](#)
- [Connectors & Cables](#)
- [Cord Sets](#)
- [Corrosion Resistant Devices](#)
- [Daylighting Controls](#)
- [Decora Devices](#)
- [Dimmers](#)
- [Cam-Type Devices](#)
- [Electrical Accessories](#)
- [Entertainment Accessories](#)
- [Entertainment Fixtures](#)
- [Entertainment Lighting Controls](#)
- [Entertainment Lighting Kits](#)



- >
- [Electrical](#)
- >
- [Network Solutions](#)
- >
- [Lighting Controls](#)
- >
- [Entertainment](#)
- >
- [Home Automation](#)
- >
- [Connected Home](#)
- >
- [Energy Management](#)
- >
- [Power Quality](#)



2413

Description

20 Amp, 125/250 Volt, NEMA L14-20R, 3P, 4W, Locking Connector, Industrial Grade, Grounding, - Black-White


Additional Product Information

- [Dimensional Drawing](#)
- [Wiring Diagram](#)


Product Features

Grounding: Grounding
 Amperage: 20 Amp
 Voltage: 125/250 Volt
 NEMA: L14-20R
 Pole: 3
 Wire: 4
 Cord Range: .595 - .895
 Wire Gauge: 14-10 AWG
 Blades/Contacts: Solid Brass
 Body Material: Super Tough Nylon
 Assembly Screws: Steel, Zinc Plated
 Color: Black-White
 Standards and Certifications: UL/CSA
 Warranty: Lifetime Warranty

Color: Black-White



NEMA: L14-20R



Features and Benefits

- For fast assembly Black & White devices feature:
- i,— Backed-out, color-coded brass terminal screws
- i,— Deep slotted triple drive face module and cord clamp screws
- i,— Deep wire wells with transparent wiring chambers
- Single piece 0.035 inch thick contacts with NO rivets for longest life and continuous conductivity
- Nylon face module features Amperage, Voltage, and NEMA configuration molded into face for easy identification and replacement.
- Fluted nylon housing makes it easier to grip with gloves and in debris-laden environments
- Thick-walled, super tough nylon housing resists abuse and impact
- Single piece external cord clamp includes catalogue number and NEMA configuration for easy identification
- External cord clamp accepts wire mesh connection grips
- Connectors ship with standard white and black cord clamp. Color-coded cord clamps available to identify amperage or equipment. Choose from blue, green, yellow, red, and orange.