

360R4W

60 Amp, 125 Volt, 2P, 3W, Outlet North American Pin & Sleeve Receptacle, Industrial Grade, IP67, Watertight - YELLOW



Leviton's pin and sleeve devices are easy to use. Matching amperage and voltage requirements is literally as easy as matching colors and telling time. The amperage rating is related to the size of the device; devices of the same amperage are the same size. The voltage rating is related to the location of the ground sleeve on the female device and the number of conductors. This location is based on a clock face with the key-way at the 6 o'clock position. The ground sleeve is positioned at a specific hour location, depending on the device's voltage rating.

Technical Information

Electrical Specifications

Amperage : 60 A

Current Interrupting : Certified for current interrupting at full rated current

Dielectric Voltage : 2000V for 1 min.

Endurance : Up to 1000 connects and disconnects, under load, at full rated current and voltage

Insulation Resistance : 500V for 1 min; >= 5M

Pole : 2

Temperature Rise : Max 30C after 50 cycles OL at 150 percent rated current

Voltage : 125 VAC

Wire : 3

Environmental Specifications

Corrosion Resistance : Ferrous parts immersed in 20°C, 10 percent ammonium chloride solution for 10 min

Flammability : Rated V-0 per UL 94

IP Rating : IP67/IP69K

Moisture Resistance : Per UL 1682, immersed for 24 hours in 5cm of 25°C water

Material Specifications

Arm Spring : Performance Grade Stainless Steel

Body Material : Valox 357

Cover Eyelet : Nickel-Plated Brass

Cover with Arm : Valox 357

Gasket Material : Chloroprene

Mounting Flange : Valox 357

Phase and Ground Sleeves : Brass

Sleeve Spring : Stainless Steel

Terminal Screws : Steel

Mechanical Specifications

Crush Test : 250lbs for 1 min after -25°C for 6 hrs

Impact Resistance : Drop from 30" 8 times after conditioning to -25°C for 6 hrs

Minimum Withdrawal Force : 15lbs

Product Features

Series : Standard Series

Standards and Certifications

CE Marking : Per low voltage directives 73/23/EEC, 93/68/EEC

CSA Certified : C22.2 No 182.1

IEC Rating : 60309-1 and 60309-2

UL Listed : 1682 and 1686


Warranty : 2-Year Limited

UPC Code : 07847783788


Country Of Origin : Please Contact Customer Service.

RoHS Compliant : Yes

Dimensional Diagram



UNIT	A	B	C
inch	3.50	1.89	4.37
mm	89	48	111



SPECIFICATION SUBMITTAL

JOB NAME:	CATALOG NUMBERS:	
<input type="text"/>	<input type="text"/>	<input type="text"/>
JOB NUMBER:	<input type="text"/>	<input type="text"/>

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):
+1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2021 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

