

Product designation	REVERSING CONTACTOR		
Product type designation	BGT12		
Electrical features			
Maximum operating current ($\leq 440V$)	A	12	
Contact characteristics			
Operational current Ie	AC-3 ($\leq 440V \leq 55^{\circ}C$)	A	12
Rated operational power AC-3 ($T \leq 55^{\circ}C$)	230V	kW	3.2
	400V	kW	5.7
	415V	kW	6.2
	440V	kW	5.5
	500V	kW	5
	690V	kW	5
Built-in auxiliary contacts			
	NO	1	
	NC	0	
UL technical data			
Maximum UL/CSA horsepower ratings single-phase	110V-120V	HP	0.5
	220V-240V	HP	1.5
Maximum UL/CSA horsepower ratings three-phase, 3-pole	200V-208V	HP	3
	220V-240V	HP	3
	440V-480V	HP	7.5
	550V-600V	HP	10
Mechanical features			
Terminals type	Clamp screw		
Weight	g	380	
Dimensions			
Wiring diagrams			
Certifications and compliance			
Compliance			
	IEC/EN 60947-1		
	IEC/EN 60947-4-1		
	UL508 CSA C22.2 n° 14		
Certificates			
	cULus		
ETIM classification			
ETIM 8.0	EC001037 - Motor starter/Motor starter combination		