

Product designation	REVERSING CONTACTOR		
Product type designation	BGT12		
<b>Electrical features</b>			
Maximum operating current ( $\leq 440V$ )	A	12	
<b>Contact characteristics</b>			
Operational current $I_e$	AC-3 ( $\leq 440V \leq 55^\circ C$ )	A	12
Rated operational power AC-3 ( $T \leq 55^\circ C$ )	230V	kW	3.2
	400V	kW	5.7
	415V	kW	6.2
	440V	kW	5.5
	500V	kW	5
	690V	kW	5
Built-in auxiliary contacts	NO	1	
	NC	0	
<b>UL technical data</b>			
Maximum UL/CSA horsepower ratings single-phase	110V-120V	HP	0.5
	220V-240V	HP	1.5
Maximum UL/CSA horsepower ratings three-phase, 3-pole	200V-208V	HP	3
	220V-240V	HP	3
	440V-480V	HP	7.5
	550V-600V	HP	10
<b>Mechanical features</b>			
Terminals type	Clamp screw		
Weight	g	445	
<b>Dimensions</b>			
<b>Wiring diagrams</b>			
<b>Certifications and compliance</b>			
Compliance	IEC/EN 60947-1		
	IEC/EN 60947-4-1		
	UL508 CSA C22.2 n° 14		
Certificates	cULus		
	<b>ETIM classification</b>		
ETIM 8.0	EC001037 - Motor starter/Motor starter combination		