

Product designation				Signal beacons
Product type designation				Ø62mm/2.44" 8LB6GL
General characteristics				
Diameter			mm - inch	62mm / 2.44"
Supply voltage (AC)			V	12...48
Supply voltage (DC)			V	12...48
Colour				Red
Material				Polycarbonate
IEC degree of protection				IP54
Mechanical features				
Tightening torque for terminals max			Nm	0.5
Terminals screw				Screw clamp terminals
Conductor section				
	AWG/Kcmil			
		max	16	
	IEC			
		max	mm ²	1.5
Weight			g	60
Ambient conditions				
Temperature				
	Operating temperature			
		min	°C	-20
		max	°C	+50
Dimensions				
Wiring diagrams				
Certifications and compliance				
Compliance				
	IEC/EN 60947-1			
	IEC/EN 60947-5-1			
Certificates				
	EAC			
ETIM classification				
ETIM 8.0				EC000232 - Optical module for signal tower