

Product designation				Signal beacons
Product type designation				Ø62mm/2.44"
				8LB6GL
<b>General characteristics</b>				
Diameter			mm - inch	62mm / 2.44"
Supply voltage (AC)			V	12...48
Supply voltage (DC)			V	12...48
Colour				White
Material				Polycarbonate
IEC degree of protection				IP54
<b>Mechanical features</b>				
Tightening torque for terminals max			Nm	0.5
Terminals screw				Screw clamp terminals
Conductor section				
	AWG/Kcmil			
		max	16	
	IEC			
		max	mm <sup>2</sup>	1.5
Weight			g	60
<b>Ambient conditions</b>				
Temperature				
	Operating temperature			
		min	°C	-20
		max	°C	+50
<b>Dimensions</b>				
<b>Wiring diagrams</b>				
<b>Certifications and compliance</b>				
Compliance				
	IEC/EN 60947-1			
	IEC/EN 60947-5-1			
Certificates				
	EAC			
<b>ETIM classification</b>				
ETIM 8.0				EC000232 - Optical module for signal tower