

Product designation	Signal beacons		
Product type designation	Ø62mm/2.44"		
	8LB6GL		
General characteristics			
Diameter	mm - inch	62mm / 2.44"	
Supply voltage (AC)	V	24...230	
Colour	White		
Material	Polycarbonate		
IEC degree of protection	IP54		
Mechanical features			
Tightening torque for terminals max	Nm	0.5	
Terminals screw	Screw clamp terminals		
Conductor section			
	AWG/Kcmil		
		max	16
	IEC		
		max	mm ² 1.5
Weight		g	60
Ambient conditions			
Temperature	Operating temperature		
		min	°C -20
		max	°C +50
Dimensions			
Wiring diagrams			
Certifications and compliance			
Compliance	IEC/EN 60947-1		
	IEC/EN 60947-5-1		
Certificates	EAC		
ETIM classification			
ETIM 8.0	EC000232 - Optical module for signal tower		